



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TWR2LEDALOSWW2UV 55W-112W Led WLPK 3K/4K/5K 8400-16200LM 120-347V *Lithonia Lighting - Acuity*

| | |
|------------------|---|
| Catalog Number | TWR2LEDALOSWW2UV |
| Manufacturer | Lithonia Lighting - Acuity |
| Description | The TWR2 Led Wall Pack Offers A Classic Appearance With A Traditional Shape and Is Loaded With Modern Features Including Three Adjustable Light Outputs (Alo), Three Switchable Color Temperatures (SWW) 30/40/50K CCT and A Switchable Dusk-to-Dawn Photocell. TWR2 Provides Ultimate Versatility With 18 Configurations In One Sku, Making On-The-Spot Reconfiguring Quick and Easy. TWR2 Is Powerful Yet Efficient, Delivering 8, 200 - 16, 100 Lumens and Capable Of Replacing Up to A 400W Hid While Saving Up to 86% In Ene |
| Weight per unit | 9.7 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-----------------|-----------------------------|
| average life | 100,000 |
| dimensions | 7.9x17.1x9.2 IN |
| dimnable | Yes |
| Hardware | Yes |
| Lamp Included | Yes |
| Lamp Type | LED - Static |
| lumens | 12,100 LM,16,100 LM,8200 LM |
| Material | Aluminum |
| Number of Lamps | 1 |
| Power Source | Hardwired |
| Shape | Rectangular |
| Voltage Rating | 120-347 |
| Warranty | 5 |
| Wattage | 112 |

Material, Color, and Finish

| | |
|-----------------------------|------------------|
| Color | Bronze |
| color rendering index (cri) | 80 |
| color temperature | 3000 ,4000 ,5000 |
| Finish | Textured |
| Lens Material | Glass |
| Style | Traditional |

Dimensions and Weight

| | |
|--------|------|
| Height | 9.2 |
| Length | 7.9 |
| Width | 17.1 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 55W-112W LED WLPK 3K/4K/5K 8400-16200LM 120-347V |
| extra long description | LITH TWR2 LED ALO SWW2 UVOLT PE DDB |
| Features | Contractor Select |
| Long Description | The TWR2 LED wall pack offers a classic appearance with a traditional shape and is loaded with modern features including three adjustable light outputs (ALO), three switchable color temperatures (SWW) 30/40/50K CCT and a switchable dusk-to-dawn photocell. TWR2 provides ultimate versatility with 18 configurations in one SKU, making on-the-spot reconfiguring quick and easy. TWR2 is powerful yet efficient, delivering 8,200 - 16,100 lumens and capable of replacing up to a 400w HID while saving up to 86% in ene |
| Product Type | Wallpack |

Manufacturer Information

| | |
|---------------------------|--------------------------------|
| Brand | Lithonia Lighting |
| GTIN | 00196183390028 |
| Manufacturers Part Number | TWR2 LED ALO SWW2 UVOLT PE DDB |
| UPC | 196183390028 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING |
| Type | Wallpack |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight | 12.1 |
| Weight Per each | 9.66 |

Uses, Certifications, and Standards

| | |
|--------------------------|---------------------------------------|
| Application | Education,Hospitality,Offices & Banks |
| environmental conditions | OUTDOOR |
| Mounting | SURFACE |
| standard | C-UL-US DLC Premium,DLC Standard |