

# Eaton U47

Catalog Number: U47

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, U shape, 1-1/4"

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body	U47
	<b>UPC</b>
	662276465817
<b>Product Length/Depth</b>	<b>Product Height</b>
12 in	5.94 in
<b>Product Width</b>	<b>Product Weight</b>
2.5 in	4.2 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

3

4

12

## Product specifications

### Shape

U

### Trade size

1-1/4"

### Material

Feraloy iron alloy

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds U47 3D drawing](#)

### Catalogs

[Crouse-Hinds series Form 7 catalog page](#)

### Certification reports

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

### Installation instructions

[IF 863 - Conduit Body Wire Pulling](#)

[IF 964 - Conduit Body Wire Pulling](#)

### Specifications and datasheets

[Eaton Specification Sheet - U47](#)

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

### Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Industrial Fittings Wire Fill Chart](#)

---

Reserved.

owners.

[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton U47

Catalog Number: U47

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, U shape, 1-1/4"

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body	U47
	<b>UPC</b>
	662276465817
<b>Product Length/Depth</b>	<b>Product Height</b>
12 in	5.94 in
<b>Product Width</b>	<b>Product Weight</b>
2.5 in	4.2 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

3

4

12

## Product specifications

### Shape

U

### Trade size

1-1/4"

### Material

Feraloy iron alloy

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds U47 3D drawing](#)

### Catalogs

[Crouse-Hinds series Form 7 catalog page](#)

### Certification reports

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

### Installation instructions

[IF 863 - Conduit Body Wire Pulling](#)

[IF 964 - Conduit Body Wire Pulling](#)

### Specifications and datasheets

[Eaton Specification Sheet - U47](#)

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

### Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Industrial Fittings Wire Fill Chart](#)



Powering Business Worldwide

Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights

Eaton is a registered trademark.

All other trademarks are  
property of their respective



---

Reserved.

owners.

[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)