

Eaton U17

Catalog Number: U17

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, U shape, 1/2"

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body	U17
	UPC
	662276465800
Product Length/Depth	Product Height
7.13 in	3.69 in
Product Width	Product Weight
1.5 in	1.55 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

3

4

12

Product specifications

Shape

U

Trade size

1/2"

Material

Feraloy iron alloy

Resources

3D CAD drawing package

[Eaton Crouse-Hinds U17 3D drawing](#)

Catalogs

[Crouse-Hinds series Form 7 catalog page](#)

Certification reports

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

Installation instructions

[IF 863 - Conduit Body Wire Pulling](#)

[IF 964 - Conduit Body Wire Pulling](#)

Specifications and datasheets

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

[Eaton Specification Sheet - U17](#)

Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Industrial Fittings Wire Fill Chart](#)

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights

Eaton is a registered trademark.

All other trademarks are
property of their respective



Powering Business Worldwide



Reserved.

owners.

[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton U17

Catalog Number: U17

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, U shape, 1/2"

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body	U17
	UPC
	662276465800
Product Length/Depth	Product Height
7.13 in	3.69 in
Product Width	Product Weight
1.5 in	1.55 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

3
4
12

Product specifications

Shape

U

Trade size

1/2"

Material

Feraloy iron alloy

Resources

3D CAD drawing package

[Eaton Crouse-Hinds U17 3D drawing](#)

Catalogs

[Crouse-Hinds series Form 7 catalog page](#)

Certification reports

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

Installation instructions

[IF 863 - Conduit Body Wire Pulling](#)

[IF 964 - Conduit Body Wire Pulling](#)

Specifications and datasheets

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

[Eaton Specification Sheet - U17](#)

Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Industrial Fittings Wire Fill Chart](#)

Reserved.

owners.

[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)