

# Specifications

## Eaton UAT2R2332UFLCH



Photo is representative

Eaton meter socket, Multi position resi service, 200A, Over/under, Large hub cover plate hub mounted, #6-350 kcmil, 4-jaw, 1-phase, #8-250 kcmil, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UAT2R2332UFLCH
<b>UPC</b>	782116997817
<b>PRODUCT LENGTH/DEPTH</b>	5.38 in
<b>PRODUCT HEIGHT</b>	14.13 in
<b>PRODUCT WIDTH</b>	24.31 in
<b>PRODUCT WEIGHT</b>	29 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed



### Product specifications

**TYPE** Multiple position residential

### Resources

	service
<b>AMPERAGE RATING</b>	200A
<b>FEED TYPE</b>	Top/bottom
<b>NUMBER OF JAWS</b>	Four-jaw
<b>PHASE</b>	Single-phase
<b>ENCLOSURE</b>	063 aluminum

**UTILITY APPROVALS**

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)  
 IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)  
 KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)  
 NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)  
 OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)  
 SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)  
 FL : Tallahassee City Electric

<b>LINE</b>	#6-350 kcmil
<b>LOAD</b>	#8-250 kcmil
<b>NUMBER OF WIRES</b>	Three-wire
<b>HUB TYPE</b>	Hub cover plate
<b>CONNECTION</b>	Ground connection
<b>SECURITY</b>	Ringless
<b>VOLTAGE RATING</b>	600 V
<b>NUMBER OF SOCKETS</b>	2

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - UAT2R2332UFLCH</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

DATE:

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton UAT2R2332UFLCH



Photo is representative

Eaton meter socket, Multi position resi service, 200A, Over/under, Large hub cover plate hub mounted, #6-350 kcmil, 4-jaw, 1-phase, #8-250 kcmil, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UAT2R2332UFLCH
<b>UPC</b>	782116997817
<b>PRODUCT LENGTH/DEPTH</b>	5.38 in
<b>PRODUCT HEIGHT</b>	14.13 in
<b>PRODUCT WIDTH</b>	24.31 in
<b>PRODUCT WEIGHT</b>	29 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed



### Product specifications

**TYPE** Multiple position residential

### Resources

	service
<b>AMPERAGE RATING</b>	200A
<b>FEED TYPE</b>	Top/bottom
<b>NUMBER OF JAWS</b>	Four-jaw
<b>PHASE</b>	Single-phase
<b>ENCLOSURE</b>	063 aluminum

**UTILITY APPROVALS**

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)  
 IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)  
 KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)  
 NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)  
 OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)  
 SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)  
 FL : Tallahassee City Electric

<b>LINE</b>	#6-350 kcmil
<b>LOAD</b>	#8-250 kcmil
<b>NUMBER OF WIRES</b>	Three-wire
<b>HUB TYPE</b>	Hub cover plate
<b>CONNECTION</b>	Ground connection
<b>SECURITY</b>	Ringless
<b>VOLTAGE RATING</b>	600 V
<b>NUMBER OF SOCKETS</b>	2

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - UAT2R2332UFLCH</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

DATE:

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

