

# Eaton UAT2R2332UFLCH

Catalog Number: UAT2R2332UFLCH

Eaton meter socket, Multi position resi service, 200A, Over/under, Large hub cover plate hub mounted, #6-350 kcmil, 4-jaw, 1-phase, #8-250 kcmil, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac

## General specifications



Photo is representative

### Product Name

Eaton meter socket

### UPC

782116997817

### Product Height

14.13 in

### Product Weight

29 lb

### Certifications

UL Listed

### Catalog Number

UAT2R2332UFLCH

### Product Length/Depth

5.38 in

### Product Width

24.31 in

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

## Product specifications

### Type

Multiple position residential service

### Amperage Rating

200A

### Feed type

Top/bottom

### Number of jaws

Four-jaw

### Phase

Single-phase

### Enclosure

063 aluminum

### Utility approvals

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

FL : Tallahassee City Electric

### Line

#6-350 kcmil

### Load

#8-250 kcmil

### Number of wires

Three-wire

### Hub type

Hub cover plate

### Connection

Ground connection

### Security

## Resources

### Catalogs

Residential and Light Commercial, Metering Products, Volume 1 Tab 4

### Specifications and datasheets

Eaton Specification Sheet - UAT2R2332UFLCH

Ringless

Voltage rating

600 V

Number of sockets

2



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton UAT2R2332UFLCH

Catalog Number: UAT2R2332UFLCH

Eaton meter socket, Multi position resi service, 200A, Over/under, Large hub cover plate hub mounted, #6-350 kcmil, 4-jaw, 1-phase, #8-250 kcmil, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac

## General specifications



Photo is representative

### Product Name

Eaton meter socket

### UPC

782116997817

### Product Height

14.13 in

### Product Weight

29 lb

### Certifications

UL Listed

### Catalog Number

UAT2R2332UFLCH

### Product Length/Depth

5.38 in

### Product Width

24.31 in

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

## Product specifications

### Type

Multiple position residential service

### Amperage Rating

200A

### Feed type

Top/bottom

### Number of jaws

Four-jaw

### Phase

Single-phase

### Enclosure

063 aluminum

### Utility approvals

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

FL : Tallahassee City Electric

### Line

#6-350 kcmil

### Load

#8-250 kcmil

### Number of wires

Three-wire

### Hub type

Hub cover plate

### Connection

Ground connection

### Security

## Resources

### Catalogs

Residential and Light Commercial, Metering Products, Volume 1 Tab 4

### Specifications and datasheets

Eaton Specification Sheet - UAT2R2332UFLCH

Ringless

Voltage rating

600 V

Number of sockets

2



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)