



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UB1093 3/4 Grommet Bushing

Topaz - Southwire LLC

Catalog Number	UB1093
Manufacturer	Topaz - Southwire LLC
Description	Universal Bushing, Universal Type; 6/6 Nylon Material; 0.453 Inch; UL, Csa Approval; 1.156 Inch Diameter; 100 Per Carton Standard Package; 3/4 Inch Trade Size; Knockout Size 3/4 Inch; Thickness 0.125 Inch; Mounting Hole Diameter 1.093 Inch
Weight per unit	N/A
Product Category	Plastic

Features

Material	6/6 Nylon
----------	-----------

Dimensions and Weight

Diameter	1.156 Inch
Height	0.453 INCH

Descriptions

Additional Information	Knockout Size 3/4 Inch; Thickness 0.125 Inch; Mounting Hole Diameter 1.093 Inch; Inside Diameter 0.812 Inch; Color Black
Commodity Description	Rigid Conduit Fittings - Plastic
Description	3/4 GROMMET BUSHING
extra long description	UNIVERSAL TYPE; 6/6 NYLON MATERIAL; 0.453 INCH; UL, CSA APPROVAL; 1.156 INCH DIAMETER; 100 PER CARTON STANDARD PACKAGE; 3/4 INCH TRADE SIZE; KNOCKOUT SIZE 3/4 INCH; THICKNESS 0.125 INCH; MOUNTING HOLE DIAMETER 1.093 INCH; INSIDE DIAMETER 0.812 INCH; COLOR BLACK
Long Description	UNIVERSAL BUSHING, UNIVERSAL TYPE; 6/6 NYLON MATERIAL; 0.453 INCH; UL, CSA APPROVAL; 1.156 INCH DIAMETER; 100 PER CARTON STANDARD PACKAGE; 3/4 INCH TRADE SIZE; KNOCKOUT SIZE 3/4 INCH; THICKNESS 0.125 INCH; MOUNTING HOLE DIAMETER 1.093 INCH
Product Type	Universal Bushing

Manufacturer Information

Brand	SOUTHWIRE ROUGH ELECTRICAL COMPONENTS
Manufacturers Part Number	UB1093

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	UNIVERSAL



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Trade Size	3/4 INCH
------------	----------

Packaging

Carton	1
Package	100
Standard Package	100 PER CARTON
Weight Per each	0

Uses, Certifications, and Standards

Approval	UL, CSA
----------	---------