

Specifications



Eaton UBTH4330TCH

Eaton meter socket, 1-pos commercial or resi service, 320A, Over/under, Large hub open, 3/8 inch stud, 4-jaw, 1-ph, 3/8 inch stud, Barrel lock, Lever bypass, 3-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UBTH4330TCH
UPC	786685135472
PRODUCT LENGTH/DEPTH	5.69 in
PRODUCT HEIGHT	36.63 in
PRODUCT WIDTH	15 in
PRODUCT WEIGHT	38 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications

SPECIAL FEATURES	Barrel lock provisions
TYPE	Single-position commercial or residential service
AMPERAGE RATING	320A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase
UTILITY APPROVALS	TN : Nashville Electric Service
LINE	3/8 in stud
LOAD	3/8 in stud
NUMBER OF WIRES	Three-wire
HUB TYPE	5 x 5 hub opening
SECURITY	Ringless
VOLTAGE RATING	600 V
BYPASS	Lever
NUMBER OF SOCKETS	1

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UBTH4330TCH

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications



Eaton UBTH4330TCH

Eaton meter socket, 1-pos commercial or resi service, 320A, Over/under, Large hub open, 3/8 inch stud, 4-jaw, 1-ph, 3/8 inch stud, Barrel lock, Lever bypass, 3-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UBTH4330TCH
UPC	786685135472
PRODUCT LENGTH/DEPTH	5.69 in
PRODUCT HEIGHT	36.63 in
PRODUCT WIDTH	15 in
PRODUCT WEIGHT	38 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications

SPECIAL FEATURES	Barrel lock provisions
TYPE	Single-position commercial or residential service
AMPERAGE RATING	320A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase
UTILITY APPROVALS	TN : Nashville Electric Service
LINE	3/8 in stud
LOAD	3/8 in stud
NUMBER OF WIRES	Three-wire
HUB TYPE	5 x 5 hub opening
SECURITY	Ringless
VOLTAGE RATING	600 V
BYPASS	Lever
NUMBER OF SOCKETS	1

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UBTH4330TCH

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

