



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UCES12INSWW690CR 12" 7W Led Undercab 27K/3K/35K Select 480LM

Lithonia Lighting - Acuity

Catalog Number	UCES12INSWW690CR
Manufacturer	Lithonia Lighting - Acuity
Description	Lith Uces 12IN SWW6 90CRI WH M6 Eco
Weight per unit	1.0 (lbs/each)
Product Category	Lighting

Features

average life	50,000
dimensions	12 x 2.55 x 1.07
dimmmable	Yes
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Static
lumens	400 LM,420 LM,430 LM
Material	Steel
Maximum Operating Temperature	25
Number of Lamps	1
Power Source	Hardwired
Shape	Rectangular
Voltage Rating	120
Warranty	5
Wattage	6.5

Material, Color, and Finish

Color	White
color rendering index (cri)	90
color temperature	2700 ,3000 ,3500 ,Variable
Finish	Gloss
Lens Color	WHITE
Lens Material	Acrylic
Style	CONTEMPORARY

Dimensions and Weight

Height	1.07
Length	12
Width	2.55



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	12" 7W LED UNDERCAB 27K/3K/35K SELECT 480LM
Features	Contractor Select
Long Description	LITH UCES 12IN SWW6 90CRI WH M6 Eco
Product Type	Undercabinet

Manufacturer Information

Brand	JUNO
GTIN	00196182177392
Manufacturers Part Number	UCES 12IN SWW6 90CRI WH M6
UPC	196182177392

Taxonomies, Classifications, and Categories

Category Description	LED TRACK, RAIL, TASK & UNDERCABINET LIGHTING
Type	Undercabinet

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Package	6
Weight	1
Weight Per each	1

Uses, Certifications, and Standards

Application	Hospitality,Residential,Retail
environmental conditions	Indoor
Mounting	SURFACE
standard	cULCA Title 24,ENERGY STAR,JA8