



Enclosures

SINGLE RESIDENCE SERVICE ENCLOSURES

- 18GA Galvanize Steel
- Captive Cover Screws
- Screw/Nail Holes on Sides
- Open back to simplify splitter mounting and connection before installation of service box.



Cat. No.	Features	Dimension (Excluding Bracket)				Color	Std. Pkg.
		Width	Height	Depth	Cu. In.		
UM1020-TV	With Embossed "TELEVISION" Text	14-7/8"	4-5/8"	1-5/8"	111.8	Beige	10
UM900-TV	With Embossed "TV" Text	3-3/4"	7"	2"	52.5	Beige	20
UM1020-PH	With Embossed "TELEPHONE" Text & Protector Bracket	14-7/8"	4-5/8"	2-7/8"	197.8	Beige	10
UM900-PH	With Embossed "PHONE" Text	3-3/4"	7"	2"	52.5	Beige	20


NEMA Enclosures



UM1020-TV



UM900-TV



UM1020-PH



UM900-PH

MODULAR INTERFACE SERVICE ENCLOSURES

- 18GA Galvanize Steel
- 2 Captive Cover Screws
- 9 Screw/Nail Holes on Sides
- Plywood back to simplify protector mounting and connection before installation of service box.



Cat. No.	Description	Dimension (Excluding Bracket)				Color	Std. Pkg.
		Width	Height	Depth	Cu. In.		
UM1100-TV	With Embossed "TELEVISION" Text & Plywood Back Bracket	14-7/8"	11"	4-7/8"	797.6	Beige	5
UM1100-PH	With Embossed "TELEPHONE" Text & Plywood Back Bracket	14-7/8"	11"	4-7/8"	797.6	Beige	5
UM1100-PH-GB	With Embossed "TELEPHONE" Text & Plywood Back Bracket With Installed Ground Bar	14-7/8"	11"	4-7/8"	797.6	Beige	5



UM1100-TV



UM1100-PH
UM1100-PH-GB

Certification:

- File 33033655

Enclosures

SINGLE RESIDENCE SERVICE ENCLOSURES

- 18GA Galvanize Steel
- Captive Cover Screws
- Screw/Nail Holes on Sides
- Open back to simplify splitter mounting and connection before installation of service box.



Cat. No.	Features	Dimension (Excluding Bracket)				Color	Std. Pkg.
		Width	Height	Depth	Cu. In.		
UM1020-TV	With Embossed "TELEVISION" Text	14-7/8"	4-5/8"	1-5/8"	111.8	Beige	10
UM900-TV	With Embossed "TV" Text	3-3/4"	7"	2"	52.5	Beige	20
UM1020-PH	With Embossed "TELEPHONE" Text & Protector Bracket	14-7/8"	4-5/8"	2-7/8"	197.8	Beige	10
UM900-PH	With Embossed "PHONE" Text	3-3/4"	7"	2"	52.5	Beige	20


NEMA Enclosures



UM1020-TV



UM900-TV



UM1020-PH



UM900-PH

MODULAR INTERFACE SERVICE ENCLOSURES


- 18GA Galvanize Steel
- 2 Captive Cover Screws
- 9 Screw/Nail Holes on Sides
- Plywood back to simplify protector mounting and connection before installation of service box.



Cat. No.	Description	Dimension (Excluding Bracket)				Color	Std. Pkg.
		Width	Height	Depth	Cu. In.		
UM1100-TV	With Embossed "TELEVISION" Text & Plywood Back Bracket	14-7/8"	11"	4-7/8"	797.6	Beige	5
UM1100-PH	With Embossed "TELEPHONE" Text & Plywood Back Bracket	14-7/8"	11"	4-7/8"	797.6	Beige	5
UM1100-PH-GB	With Embossed "TELEPHONE" Text & Plywood Back Bracket With Installed Ground Bar	14-7/8"	11"	4-7/8"	797.6	Beige	5



UM1100-TV



UM1100-PH
UM1100-PH-GB

Certification:

- File 33033655