

# Specifications

## Eaton UNRRS213BEUSE

Eaton meter socket, 3 5/16 in hub opening, 200A, Overhead, Hub opening, #6-350 kcmil, Four-jaw, Single-phase, #6-350 kcmil, Sockets:1, Three-wire, Ring, 600V



### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UNRRS213BEUSE
<b>UPC</b>	786685217888
<b>PRODUCT LENGTH/DEPTH</b>	4.48 in
<b>PRODUCT HEIGHT</b>	15.11 in
<b>PRODUCT WIDTH</b>	11.22 in
<b>PRODUCT WEIGHT</b>	18 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	3 5/16 in hub opening
<b>AMPERAGE RATING</b>	200A
<b>FEED TYPE</b>	Overhead
<b>NUMBER OF JAWS</b>	Four-jaw
<b>PHASE</b>	Single-phase
<b>UTILITY APPROVALS</b>	TX : CenterPoint Energy (HL&P/Reliant)
<b>LINE</b>	#6-350 kcmil
<b>LOAD</b>	#6-350 kcmil
<b>ENCLOSURE MATERIAL</b>	16 GA GALV STEEL
<b>NUMBER OF WIRES</b>	Three-wire
<b>HUB TYPE</b>	Hub opening
<b>SECURITY</b>	Ring
<b>VOLTAGE RATING</b>	600 V
<b>NUMBER OF SOCKETS</b>	1

## Resources

### CATALOGS

[Residential and Light Commercial, Metering Products, Volume 1 Tab 4](#)

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - UNRRS213BEUSE](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton UNRRS213BEUSE

Eaton meter socket, 3 5/16 in hub opening, 200A, Overhead, Hub opening, #6-350 kcmil, Four-jaw, Single-phase, #6-350 kcmil, Sockets:1, Three-wire, Ring, 600V



### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UNRRS213BEUSE
<b>UPC</b>	786685217888
<b>PRODUCT LENGTH/DEPTH</b>	4.48 in
<b>PRODUCT HEIGHT</b>	15.11 in
<b>PRODUCT WIDTH</b>	11.22 in
<b>PRODUCT WEIGHT</b>	18 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed

## Product specifications

<b>TYPE</b>	3 5/16 in hub opening
<b>AMPERAGE RATING</b>	200A
<b>FEED TYPE</b>	Overhead
<b>NUMBER OF JAWS</b>	Four-jaw
<b>PHASE</b>	Single-phase
<b>UTILITY APPROVALS</b>	TX : CenterPoint Energy (HL&P/Reliant)
<b>LINE</b>	#6-350 kcmil
<b>LOAD</b>	#6-350 kcmil
<b>ENCLOSURE MATERIAL</b>	16 GA GALV STEEL
<b>NUMBER OF WIRES</b>	Three-wire
<b>HUB TYPE</b>	Hub opening
<b>SECURITY</b>	Ring
<b>VOLTAGE RATING</b>	600 V
<b>NUMBER OF SOCKETS</b>	1

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - UNRRS213BEUSE</a>

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

