

Specifications



Eaton UTE4213BCH

Eaton meter socket, Comm, 200A, Over/under, 3-5/16 inch hub open, #6-350 kcmil, 4-jaw, 1-ph, #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UTE4213BCH
UPC	786685351087
PRODUCT LENGTH/DEPTH	4.94 in
PRODUCT HEIGHT	19 in
PRODUCT WIDTH	13 in
PRODUCT WEIGHT	25 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed



Powering Business Worldwide

Product specifications

TYPE	Commercial
AMPERAGE RATING	200A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase
UTILITY APPROVALS	ME : Central Maine Power ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company) MD : First Energy (Potomac Edison) VA : First Energy (Potomac Edison) WV : First Energy (Mon Power) NJ : First Energy (Jersey Central Power and Light) OH : First Energy (Ohio Edison, Toledo Edison, The Illuminating Company) PA : First Energy (Allegheny Power, MET ED, Penelec, West Penn Power) TX : Pedernales Electric Cooperative WI : WE Energies / Wisconsin Public Service (WPS)
LINE	#6-350 kcmil
LOAD	#6-350 kcmil
NUMBER OF WIRES	Three-wire
HUB TYPE	3-5/16 in hub opening
SECURITY	Ringless
VOLTAGE RATING	600 V
BYPASS	Lever
NUMBER OF SOCKETS	1

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UTE4213BCH
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

