

Eaton UTE7213THLCH

Catalog Number: UTE7213THLCH

Eaton meter socket, Comm, 200A, Over/under, 5x5 inch hub open, #6-350 kcmil, 7-jaw, 1-ph, #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac



General specifications

Product Name

Eaton meter socket

Catalog Number

UTE7213THLCH

UPC

786685351278

Product Length/Depth

4.94 in

Product Height

19 in

Product Width

13 in

Product Weight

25 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Product specifications

Type

Commercial

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Seven-jaw

Phase

Single-phase

Utility approvals

TX : Oncor

TX : Pedernales Electric Cooperative

Line

#6-350 kcmil

Load

#6-350 kcmil

Number of wires

Three-wire

Hub type

5 x 5 hub opening

Connection

Ground connection

Security

Ringless

Voltage rating

600 V

Bypass

Lever

Number of sockets

1

Resources

Brochures

[Single Meter Sockets](#)

Specifications and datasheets

[Eaton Specification Sheet - UTE7213THLCH](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton UTE7213THLCH

Catalog Number: UTE7213THLCH

Eaton meter socket, Comm, 200A, Over/under, 5x5 inch hub open, #6-350 kcmil, 7-jaw, 1-ph, #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac



General specifications

Product Name

Eaton meter socket

Catalog Number

UTE7213THLCH

UPC

786685351278

Product Length/Depth

4.94 in

Product Height

19 in

Product Width

13 in

Product Weight

25 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Product specifications

Type

Commercial

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Seven-jaw

Phase

Single-phase

Utility approvals

TX : Oncor

TX : Pedernales Electric Cooperative

Line

#6-350 kcmil

Load

#6-350 kcmil

Number of wires

Three-wire

Hub type

5 x 5 hub opening

Connection

Ground connection

Security

Ringless

Voltage rating

600 V

Bypass

Lever

Number of sockets

1

Resources

Brochures

[Single Meter Sockets](#)

Specifications and datasheets

[Eaton Specification Sheet - UTE7213THLCH](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)