

# Specifications

## Eaton UT4R1121BCH



Eaton meter socket, Multi position commercial or resi service, 100A, Over/under, 3-5/16 inch hub open, #6-250 kcmil, Four-jaw, 1-ph, #8-2/0 AWG, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UT4R1121BCH
<b>UPC</b>	782116094639
<b>PRODUCT LENGTH/DEPTH</b>	4.5 in
<b>PRODUCT HEIGHT</b>	14.13 in
<b>PRODUCT WIDTH</b>	40.63 in
<b>PRODUCT WEIGHT</b>	40 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed
<b>PRODUCT TYPE</b>	Meter socket

## Product specifications

<b>TYPE</b>	Multiple position commercial or residential service
<b>AMPERAGE RATING</b>	100A
<b>FEED TYPE</b>	Top/bottom
<b>NUMBER OF JAWS</b>	Four-jaw
<b>PHASE</b>	Single-phase
<b>UTILITY APPROVALS</b>	ME : Central Maine Power ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company) SC : South Carolina Electric and Gas (SCE&G) AR : Entergy LA : Entergy MS : Entergy TX : Entergy
<b>LINE</b>	#6-250 kcmil
<b>LOAD</b>	#8-2/0 AWG
<b>NUMBER OF WIRES</b>	Three-wire
<b>HUB TYPE</b>	3-5/16 in hub opening
<b>SECURITY</b>	Ringless
<b>VOLTAGE RATING</b>	600 V
<b>NUMBER OF SOCKETS</b>	4

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - UT4R1121BCH</a>
<b>WARRANTY GUIDES</b>	<a href="#">Selling Policy 25-000 - Distribution and Control Products and Services</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
[Eaton.com](http://Eaton.com)

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

