

Specifications



Eaton UTE5213CCH

Eaton meter socket, Comm, 200A, Over/under, 3-5/16 inch hub cover plate, #6-350 kcmil, 5-jaw, 1-ph, #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, Three-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UTE5213CCH
UPC	786685271361
PRODUCT LENGTH/DEPTH	4.94 in
PRODUCT HEIGHT	19 in
PRODUCT WIDTH	13 in
PRODUCT WEIGHT	26 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed



Powering Business Worldwide

Product specifications

TYPE	Commercial
AMPERAGE RATING	200A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Five-jaw
PHASE	Single-phase
UTILITY APPROVALS	ME : Central Maine Power NM : El Paso Electric TX : El Paso Electric ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company) NM : Public Service Company of New Mexico (PNM) WI : WE Energies / Wisconsin Public Service (WPS)
LINE	#6-350 kcmil
LOAD	#6-350 kcmil
NUMBER OF WIRES	Three-wire
HUB TYPE	3-5/16 in hub cover plate
SECURITY	Ringless
VOLTAGE RATING	600 V
BYPASS	Lever
NUMBER OF SOCKETS	1

Resources

CATALOGS

[Residential and Light Commercial, Metering Products, Volume 1 Tab 4](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - UTE5213CCH](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



© 2025 Eaton. All Rights Reserved.



Specifications



Eaton UTE5213CCH

Eaton meter socket, Comm, 200A, Over/under, 3-5/16 inch hub cover plate, #6-350 kcmil, 5-jaw, 1-ph, #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, Three-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UTE5213CCH
UPC	786685271361
PRODUCT LENGTH/DEPTH	4.94 in
PRODUCT HEIGHT	19 in
PRODUCT WIDTH	13 in
PRODUCT WEIGHT	26 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed



Powering Business Worldwide

Product specifications

TYPE	Commercial
AMPERAGE RATING	200A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Five-jaw
PHASE	Single-phase
UTILITY APPROVALS	ME : Central Maine Power NM : El Paso Electric TX : El Paso Electric ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company) NM : Public Service Company of New Mexico (PNM) WI : WE Energies / Wisconsin Public Service (WPS)
LINE	#6-350 kcmil
LOAD	#6-350 kcmil
NUMBER OF WIRES	Three-wire
HUB TYPE	3-5/16 in hub cover plate
SECURITY	Ringless
VOLTAGE RATING	600 V
BYPASS	Lever
NUMBER OF SOCKETS	1

Resources

CATALOGS

[Residential and Light Commercial, Metering Products, Volume 1 Tab 4](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - UTE5213CCH](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



© 2025 Eaton. All Rights Reserved.

