

# Specifications



## Eaton UTRS101CE

Eaton meter socket, 1-pos resi service, 125A, Over, 3-5/16 inch hub cover plate, #8-2/0 AWG, 4-jaw, 1-phase, #8-2/0 AWG, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UTRS101CE
<b>UPC</b>	786685217727
<b>PRODUCT LENGTH/DEPTH</b>	3.61 in
<b>PRODUCT HEIGHT</b>	11.05 in
<b>PRODUCT WIDTH</b>	8.22 in
<b>PRODUCT WEIGHT</b>	7 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed

## Product specifications

<b>TYPE</b>	Single-position residential service
<b>AMPERAGE RATING</b>	125A
<b>FEED TYPE</b>	Overhead
<b>NUMBER OF JAWS</b>	Four-jaw
<b>PHASE</b>	Single-phase
<b>UTILITY APPROVALS</b>	<p>ME : Central Maine Power</p> <p>ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company)</p> <p>MO : Empire District Electric</p> <p>OK : Empire District Electric</p> <p>FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)</p> <p>IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)</p> <p>KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)</p> <p>NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)</p> <p>OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)</p> <p>SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)</p> <p>NM : Public Service Company of New Mexico (PNM)</p> <p>SC : South Carolina Electric and Gas (SCE&amp;G)</p>
<b>LINE</b>	#8-2/0 AWG
<b>LOAD</b>	#8-2/0 AWG
<b>NUMBER OF WIRES</b>	Three-wire
<b>HUB TYPE</b>	3-5/16 in hub cover plate
<b>SECURITY</b>	Ringless

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - UTRS101CE</a>

<b>VOLTAGE RATING</b>	600 V
<b>NUMBER OF SOCKETS</b>	1

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
[Eaton.com](http://Eaton.com)

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton UTRS101CE

Eaton meter socket, 1-pos resi service, 125A, Over, 3-5/16 inch hub cover plate, #8-2/0 AWG, 4-jaw, 1-phase, #8-2/0 AWG, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UTRS101CE
<b>UPC</b>	786685217727
<b>PRODUCT LENGTH/DEPTH</b>	3.61 in
<b>PRODUCT HEIGHT</b>	11.05 in
<b>PRODUCT WIDTH</b>	8.22 in
<b>PRODUCT WEIGHT</b>	7 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed

## Product specifications

<b>TYPE</b>	Single-position residential service
<b>AMPERAGE RATING</b>	125A
<b>FEED TYPE</b>	Overhead
<b>NUMBER OF JAWS</b>	Four-jaw
<b>PHASE</b>	Single-phase
<b>UTILITY APPROVALS</b>	<p>ME : Central Maine Power</p> <p>ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company)</p> <p>MO : Empire District Electric</p> <p>OK : Empire District Electric</p> <p>FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)</p> <p>IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)</p> <p>KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)</p> <p>NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)</p> <p>OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)</p> <p>SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)</p> <p>NM : Public Service Company of New Mexico (PNM)</p> <p>SC : South Carolina Electric and Gas (SCE&amp;G)</p>
<b>LINE</b>	#8-2/0 AWG
<b>LOAD</b>	#8-2/0 AWG
<b>NUMBER OF WIRES</b>	Three-wire
<b>HUB TYPE</b>	3-5/16 in hub cover plate
<b>SECURITY</b>	Ringless

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - UTRS101CE</a>

<b>VOLTAGE RATING</b>	600 V
<b>NUMBER OF SOCKETS</b>	1

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
[Eaton.com](http://Eaton.com)

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

