

Specifications

Photo is representative

Eaton UTH7233UCH

Eaton meter socket, 1-pos commercial or resi service, 200A, Over/under, 5x5 inch hub cover plate, #6-350 kcmil, 7-jaw, 3-ph, #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 4-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UTH7233UCH
UPC	782116104208
PRODUCT LENGTH/DEPTH	5.63 in
PRODUCT HEIGHT	27 in
PRODUCT WIDTH	16 in
PRODUCT WEIGHT	31 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications

TYPE	Single-position commercial or residential service
AMPERAGE RATING	200A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Seven-jaw
PHASE	Three-phase
UTILITY APPROVALS	AR : Entergy LA : Entergy MS : Entergy TX : Entergy
LINE	#6-350 kcmil
LOAD	#6-350 kcmil
NUMBER OF WIRES	Four-wire
HUB TYPE	5 x 5 hub cover plate
SECURITY	Ringless
VOLTAGE RATING	600 V
BYPASS	Lever
NUMBER OF SOCKETS	1

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UTH7233UCH
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Photo is representative

Eaton UTH7233UCH

Eaton meter socket, 1-pos commercial or resi service, 200A, Over/under, 5x5 inch hub cover plate, #6-350 kcmil, 7-jaw, 3-ph, #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 4-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UTH7233UCH
UPC	782116104208
PRODUCT LENGTH/DEPTH	5.63 in
PRODUCT HEIGHT	27 in
PRODUCT WIDTH	16 in
PRODUCT WEIGHT	31 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications

TYPE	Single-position commercial or residential service
AMPERAGE RATING	200A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Seven-jaw
PHASE	Three-phase
UTILITY APPROVALS	AR : Entergy LA : Entergy MS : Entergy TX : Entergy
LINE	#6-350 kcmil
LOAD	#6-350 kcmil
NUMBER OF WIRES	Four-wire
HUB TYPE	5 x 5 hub cover plate
SECURITY	Ringless
VOLTAGE RATING	600 V
BYPASS	Lever
NUMBER OF SOCKETS	1

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UTH7233UCH
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

