

Specifications



Eaton UTRS213CE

Eaton meter socket, 1-pos resi service, 200 A, Over/under, 3-5/16 inch hub cover plate, #6-350 kcmil, 4-jaw, 1-ph, #6-350 kcmil, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UTRS213CE
UPC	786685217901
PRODUCT LENGTH/DEPTH	4.48 in
PRODUCT HEIGHT	15.11 in
PRODUCT WIDTH	11.22 in
PRODUCT WEIGHT	14 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications

TYPE	Single-position residential service
AMPERAGE RATING	200A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase
UTILITY APPROVALS	ME : Central Maine Power MI : DTE Energy (Detroit Edison) NM : El Paso Electric TX : El Paso Electric AL : Alabama Power MO : Empire District Electric OK : Empire District Electric AR : Entergy LA : Entergy MS : Entergy TX : Entergy GA : Georgia Power FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) TX : Oncor TX : Pedernales Electric

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UTRS213CE

	Cooperative SC : South Carolina Electric and Gas (SCE&G)
LINE	#6-350 kcmil
LOAD	#6-350 kcmil
NUMBER OF WIRES	Three-wire
HUB TYPE	3-5/16 in hub cover plate
SECURITY	Ringless
VOLTAGE RATING	600 V
NUMBER OF SOCKETS	1

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Eaton UTRS213CE

Eaton meter socket, 1-pos resi service, 200 A, Over/under, 3-5/16 inch hub cover plate, #6-350 kcmil, 4-jaw, 1-ph, #6-350 kcmil, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UTRS213CE
UPC	786685217901
PRODUCT LENGTH/DEPTH	4.48 in
PRODUCT HEIGHT	15.11 in
PRODUCT WIDTH	11.22 in
PRODUCT WEIGHT	14 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications

TYPE	Single-position residential service
AMPERAGE RATING	200A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase
UTILITY APPROVALS	ME : Central Maine Power MI : DTE Energy (Detroit Edison) NM : El Paso Electric TX : El Paso Electric AL : Alabama Power MO : Empire District Electric OK : Empire District Electric AR : Entergy LA : Entergy MS : Entergy TX : Entergy GA : Georgia Power FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) TX : Oncor TX : Pedernales Electric

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UTRS213CE

	Cooperative SC : South Carolina Electric and Gas (SCE&G)
LINE	#6-350 kcmil
LOAD	#6-350 kcmil
NUMBER OF WIRES	Three-wire
HUB TYPE	3-5/16 in hub cover plate
SECURITY	Ringless
VOLTAGE RATING	600 V
NUMBER OF SOCKETS	1

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

