

# Specifications



## Eaton UTRS213BE

Eaton meter socket, 1-pos resi service, 200 A, Over/under, 3-5/16 inch hub open, #6-350 kcmil, 4-jaw, 1-ph, #6-350 kcmil, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UTRS213BE
<b>UPC</b>	786685217758
<b>PRODUCT LENGTH/DEPTH</b>	4.48 in
<b>PRODUCT HEIGHT</b>	15.11 in
<b>PRODUCT WIDTH</b>	11.22 in
<b>PRODUCT WEIGHT</b>	14 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed

### Product specifications

<b>TYPE</b>	Single-position residential service
<b>AMPERAGE RATING</b>	200A
<b>FEED TYPE</b>	Top/bottom
<b>NUMBER OF JAWS</b>	Four-jaw
<b>PHASE</b>	Single-phase

ME : Central Maine Power MI : DTE Energy (Detroit Edison) MO : Empire District Electric OK : Empire District Electric AR : Entergy LA : Entergy MS : Entergy TX : Entergy TN : Knoxville Utility Board (KUB) TX : Oncor NM : Public Service Company of New Mexico (PNM) CT : United Illuminating (UI) SC : South Carolina Electric and Gas (SCE&G) NM : Texas-New Mexico Power (TNMP) TX : Texas-New Mexico Power

### UTILITY APPROVALS

# Specifications



## Eaton UTRS213BE

Eaton meter socket, 1-pos resi service, 200 A, Over/under, 3-5/16 inch hub open, #6-350 kcmil, 4-jaw, 1-ph, #6-350 kcmil, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UTRS213BE
<b>UPC</b>	786685217758
<b>PRODUCT LENGTH/DEPTH</b>	4.48 in
<b>PRODUCT HEIGHT</b>	15.11 in
<b>PRODUCT WIDTH</b>	11.22 in
<b>PRODUCT WEIGHT</b>	14 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed

### Product specifications

<b>TYPE</b>	Single-position residential service
<b>AMPERAGE RATING</b>	200A
<b>FEED TYPE</b>	Top/bottom
<b>NUMBER OF JAWS</b>	Four-jaw
<b>PHASE</b>	Single-phase

ME :  
Central  
Maine  
Power  
MI : DTE  
Energy  
(Detroit  
Edison)  
MO :  
Empire  
District  
Electric  
OK :  
Empire  
District  
Electric  
AR :  
Entergy  
LA :  
Entergy  
MS :  
Entergy  
TX :  
Entergy  
TN :  
Knoxville  
Utility  
Board  
(KUB)  
TX : Oncor  
NM : Public  
Service  
Company  
of New  
Mexico  
(PNM)  
CT : United  
Illuminating  
(UI)  
SC : South  
Carolina  
Electric and  
Gas  
(SCE&G)  
NM :  
Texas-New  
Mexico  
Power  
(TNMP)  
TX : Texas-  
New  
Mexico  
Power

### UTILITY APPROVALS