

Specifications



Photo is representative



Eaton V48M28T12EE

Eaton General purpose ventilated transformer, DT-3 (3-phase), PV 480V, Taps: 2 at +2.5% /4 at -2.5%, SV 208Y/120V, 150°C rise w/ 200°C insulation system, 112.5 kVA, EE

General specifications

PRODUCT NAME	Eaton General purpose ventilated transformer
CATALOG NUMBER	V48M28T12EE
UPC	786680019371
PRODUCT LENGTH/DEPTH	23.42 in
PRODUCT HEIGHT	32.02 in
PRODUCT WIDTH	28.22 in
PRODUCT WEIGHT	793 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	NEMA TP-1 Compliant
CERTIFICATIONS	UL Listed
CATALOG NOTES	NEMA TP-1 efficient

Physical Attributes

COIL MATERIAL	Aluminum
FRAME	916A
TAP SIZE	2 at +2.5% FCAN, 4 at -2.5% FCBN
TYPE	Dry Type Distribution Transformer

Miscellaneous

WEATHERSHIELD	WS19
---------------	------

Performance Ratings

FREQUENCY RATING	60 Hz
PRIMARY VOLTAGE	480 V
SECONDARY VOLTAGE	208 Y/120 V
TEMPERATURE RISE	150 °C rise
VOLT AMPERE RATING	112.5 kVA

Resources

CATALOGS	Commercial Distribution Transformers, Volume 2, Tab 2
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - V48M28T12EE

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications



Photo is representative



Eaton V48M28T12EE

Eaton General purpose ventilated transformer, DT-3 (3-phase), PV 480V, Taps: 2 at +2.5% /4 at -2.5%, SV 208Y/120V, 150°C rise w/ 200°C insulation system, 112.5 kVA, EE

General specifications

PRODUCT NAME	Eaton General purpose ventilated transformer
CATALOG NUMBER	V48M28T12EE
UPC	786680019371
PRODUCT LENGTH/DEPTH	23.42 in
PRODUCT HEIGHT	32.02 in
PRODUCT WIDTH	28.22 in
PRODUCT WEIGHT	793 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	NEMA TP-1 Compliant
CERTIFICATIONS	UL Listed
CATALOG NOTES	NEMA TP-1 efficient



Powering Business Worldwide

Physical Attributes

COIL MATERIAL	Aluminum
FRAME	916A
TAP SIZE	2 at +2.5% FCAN, 4 at -2.5% FCBN
TYPE	Dry Type Distribution Transformer

Miscellaneous

WEATHERSHIELD	WS19
---------------	------

Performance Ratings

FREQUENCY RATING	60 Hz
PRIMARY VOLTAGE	480 V
SECONDARY VOLTAGE	208 Y/120 V
TEMPERATURE RISE	150 °C rise
VOLT AMPERE RATING	112.5 kVA

Resources

CATALOGS	Commercial Distribution Transformers, Volume 2, Tab 2
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - V48M28T12EE

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

