



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **VC150IM12 150W CLG MNT V/T Fix** *Lithonia Lighting - Acuity*

Catalog Number	VC150IM12
Manufacturer	Lithonia Lighting - Acuity
Description	Utility Ceiling-Mounted Fixtures For Entrances, Hallways, Closets, Tunnels or Other Utility Applications
Weight per unit	2.5 (lbs/each)
Product Category	Incandescent Vapor Tight Light

### **Features**

average life	100,000
Ballast Type	Not Applicable
Hardware	Yes
Lamp Included	NO
Lamp Type	Incandescent
Material	Aluminum
Number of Lamps	1
pallet quantity	288
Power Source	Hardwired
Shape	Round
Socket Type	Medium: Screw
Voltage Rating	120
Warranty	2
Wattage	150

### **Material, Color, and Finish**

Color	Gray
Finish	Gloss
fixture material	aluminum
Lens Material	Glass
Style	Traditional

### **Dimensions and Weight**

Height	9.0000
Length	4.5000
Width	4.5000



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	150W CLG MNT V/T FIX
extra long description	LITH VC150I M12 Utility vapor tight
Long Description	Utility ceiling-mounted fixtures for entrances, hallways, closets, tunnels or other utility applications
Product Type	Wallpack
Special Features	Utility wall-, ceiling- or pendant-mounted fixtures for entrances, hallways, closets, tunnels or other utility applications. Incandescent, fluorescent, metal halide or high pressure sodium sources are available.

## Manufacturer Information

Brand	Lithonia Lighting
GTIN	00745973817704
Manufacturers Part Number	VC150IM12
UPC	745973817704

## Taxonomies, Classifications, and Categories

Category Description	LED HAZARDOUS LOCATION & VAPOR TIGHT LIGHTING
Type	Wall Pack

## Packaging

Carton	1
Package	12
Weight	2.0000
Weight Per each	2.5

## Uses, Certifications, and Standards

Application	Education,Hospitality,Offices & Banks
environmental conditions	OUTDOOR
Mounting	SURFACE
standard	cUL