



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **WF4SWW590CRIMWM6 4" 9W Led Wafer 27K/3K/35K/4K/5K 650LM** *Lithonia Lighting - Acuity*

|                  |   |
|------------------|---|
| Catalog Number   | WF4SWW590CRIMWM6  |
| Manufacturer     | Lithonia Lighting - Acuity  |
| Description      | The 4-Inch Juno® Wafer™ Led Downlights With Switchable White Provides High-Quality Light Output and Efficiency and Features A Switch For Easy Color Temperature Adjustment, While Eliminating The Need For Recessed Housings. The Innovative Switchable White Feature Incorporates A Switch On Each Fixture For Simple Color Temperature Adjustment. Too Warm or Too Cool? Simply Toggle The Integrated Switch to Your Desired Setting (3000K Factory Default) and You Are Done! Whatever Your Application, Luminaires With Swi |
| Weight per unit  | 1.5 (lbs/each)  |
| Product Category | Lighting  |

### **Features**

|                               |                 |
|-------------------------------|-----------------|
| average life                  | 50,000          |
| dimensions                    | 4.7 x 1.1 x 1.1 |
| dimmable                      | Yes             |
| Hardware                      | Yes             |
| Lamp Included                 | Yes             |
| Lamp Type                     | LED - Dynamic   |
| lumens                        | 670 LM          |
| Material                      | Polycarbonate   |
| Maximum Operating Temperature | 25              |
| Power Source                  | Hardwired       |
| Shape                         | Round           |
| Voltage Rating                | 120             |
| Warranty                      | 3               |
| Wattage                       | 9               |

### **Material, Color, and Finish**

|                             |  |
|-----------------------------|--|
| Color                       | White                                  |
| color rendering index (cri) | 90                                     |
| color temperature           | 2700 ,3000 ,3500 ,4000 ,5000 ,Variable |
| Finish                      | Matte                                  |
| Lens Color                  | WHITE                                  |
| Lens Material               | Polycarbonate                          |
| Style                       | CONTEMPORARY                           |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Dimensions and Weight

|        |     |
|--------|-----|
| Height | 1.1 |
| Length | 4.7 |
| Width  | 4.7 |

## Descriptions

|                        |   |
|------------------------|---|
| Construction           | Canless,New Construction,Remodel  |
| Description            | 4" 9W LED WAFER 27K/3K/35K/4K/5K 650LM  |
| extra long description | LITH WF4 SWW5 90CRI MW M6 4IN wafer   |
| Features               | Contractor Select   |
| Long Description       | The 4-inch Juno® Wafer™ LED Downlights with Switchable White provides high-quality light output and efficiency and features a switch for easy color temperature adjustment, while eliminating the need for recessed housings. The innovative Switchable White feature incorporates a switch on each fixture for simple color temperature adjustment. Too warm or too cool? Simply toggle the integrated switch to your desired setting (3000K factory default) and you are done! Whatever your application, luminaires with Swi |
| Product Type           | Downlight   |

## Manufacturer Information

|                           |                      |
|---------------------------|----------------------|
| Brand                     | JUNO                 |
| GTIN                      | 00194994243465       |
| Manufacturers Part Number | WF4 SWW5 90CRI MW M6 |
| UPC                       | 194994243465         |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | LED ARCHITECTURAL & SPECIFICATION LIGHTING |
| Type                 | Downlight                                  |

## Trade Size

|               |      |
|---------------|------|
| aperture size | 4 in |
|---------------|------|

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Package         | 6   |
| Weight          | 1   |
| Weight Per each | 1.5 |

## Uses, Certifications, and Standards

|                          |   |
|--------------------------|---|
| Application              | Decorative,Hospitality,Residential,Retail,Shower            |
| environmental conditions | Indoor,Outdoor  |
| Mounting                 | Recessed  |
| standard                 | CSAusCA Title 24,ENERGY STAR,FCC 47CFR Part 15 Consumer,JA8 |