



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WF6LED30K40K50KM *Delisted* 6" 14W Led Wafer 3K/4K/5K WHT 120-277V *Lithonia Lighting - Acuity*

Catalog Number	WF6LED30K40K50KM
Manufacturer	Lithonia Lighting - Acuity
Description	The 6-Inch Round Wafer™ Led Downlight With Switchable White Provides High Quality Light Output and Efficiency Featuring A Switch For Easy Color Temperature Adjustment From Warm White to Daylight During Installation - While Eliminating The Need For Recessed Housings. The Innovative, Slim Design Allows For Easy Retrofit, Remodel or New Construction Installation From Below The Ceiling. The Wafer Led Downlight Is Wet Location Listed – Making It Ideal For Use In A Breadth Of Outdoor Residential, Hospitality, CO
Weight per unit	1.7 (lbs/each)
Product Category	Lighting

Features

dimnable	Yes
Lamp Included	Yes
Lamp Type	LED - Dynamic
lumens	1100 LM
Material	Aluminum
Maximum Operating Temperature	25
pallet quantity	450
Power Source	Hardwired
Shape	Round
Voltage Rating	120-277
Warranty	5
Wattage	14

Material, Color, and Finish

Color	White
color rendering index (cri)	90
color temperature	Variable
Finish	Matte
Lens Color	WHITE
Lens Material	Polycarbonate



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Dimensions and Weight

Height	1.14
Length	6.7
Width	6.7

Descriptions

Construction	Canless,New Construction,Remodel
Description	*DELISTED* 6" 14W LED WAFER 3K/4K/5K WHT 120-277V
extra long description	LITH WF6 LED 30K40K50K MVOLT 90CRI
Long Description	The 6-inch round Wafer™ LED Downlight with Switchable White provides high quality light output and efficiency featuring a switch for easy color temperature adjustment from warm white to daylight during installation - while eliminating the need for recessed housings. The innovative, slim design allows for easy retrofit, remodel or new construction installation from below the ceiling. The Wafer LED downlight is wet location listed – making it ideal for use in a breadth of outdoor residential, hospitality, co
Product Type	Downlight

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00193047884716
Manufacturers Part Number	WF6 LED 30K40K50K MVOLT 90CRI
UPC	193047884716

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Downlight

Trade Size

aperture size	6 in
---------------	------

Packaging

Carton	1
Package	6
Weight	1.6
Weight Per each	1.7

Uses, Certifications, and Standards

Application	Education,Hospitality,House of Worship,Residential,Retail
environmental conditions	Indoor
Mounting	Recessed
standard	CSACA Title 24,ENERGY STAR,JA8