



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **WF8LED30K40K50KM 8" 20W Led Wafer 3K/4K/5K WHT 120-277V**

*Lithonia Lighting - Acuity*

|                  |   |
|------------------|---|
| Catalog Number   | WF8LED30K40K50KM  |
| Manufacturer     | Lithonia Lighting - Acuity  |
| Description      | The 8-Inch Round Wafer™ Led Downlight With Switchable White Provides High Quality Light Output and Efficiency Featuring A Switch For Easy Color Temperature Adjustment From Warm White to Daylight During Installation - While Eliminating The Need For Recessed Housings. The Innovative, Slim Design Allows For Easy Retrofit, Remodel or New Construction Installation From Below The Ceiling. The Wafer Led Downlight Is Wet Location Listed – Making It Ideal For Use In A Breadth Of Outdoor Residential, Hospitality, CO |
| Weight per unit  | 2.1 (lbs/each)  |
| Product Category | Lighting  |

### **Features**

|                               |               |
|-------------------------------|---------------|
| average life                  | 35,000        |
| dimnable                      | Yes           |
| Lamp Included                 | Yes           |
| Lamp Type                     | LED - Dynamic |
| lumens                        | 1800 LM       |
| Maximum Operating Temperature | 25            |
| media                         | Yes           |
| pallet quantity               | 300           |
| Power Source                  | Hardwired     |
| Shape                         | Round         |
| Voltage Rating                | 120-277       |
| Warranty                      | 5             |
| Wattage                       | 21            |

### **Material, Color, and Finish**

|                             |          |
|-----------------------------|----------|
| Color                       | White    |
| color rendering index (cri) | 90       |
| color temperature           | Variable |
| Finish                      | Matte    |
| Lens Color                  | WHITE    |

### **Dimensions and Weight**

|        |      |
|--------|------|
| Height | 1.13 |
| Length | 8.86 |
| Width  | 8.86 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Construction           | Canless,New Construction,Remodel  |
| Description            | 8" 20W LED WAFER 3K/4K/5K WHT 120-277V  |
| extra long description | LITH WF8 LED 30K40K50K MVOLT 90CRI  |
| Long Description       | The 8-inch round Wafer™ LED Downlight with Switchable White provides high quality light output and efficiency featuring a switch for easy color temperature adjustment from warm white to daylight during installation - while eliminating the need for recessed housings. The innovative, slim design allows for easy retrofit, remodel or new construction installation from below the ceiling. The Wafer LED downlight is wet location listed – making it ideal for use in a breadth of outdoor residential, hospitality, co |
| Product Type           | Downlight   |

## Manufacturer Information

|                           |                               |
|---------------------------|-------------------------------|
| Brand                     | Lithonia Lighting             |
| GTIN                      | 00193047884778                |
| Manufacturers Part Number | WF8 LED 30K40K50K MVOLT 90CRI |
| UPC                       | 193047884778                  |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | LED ARCHITECTURAL & SPECIFICATION LIGHTING |
| Type                 | Downlight                                  |

## Trade Size

|               |      |
|---------------|------|
| aperture size | 8 IN |
|---------------|------|

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Package         | 6   |
| Weight          | 2   |
| Weight Per each | 2.1 |

## Uses, Certifications, and Standards

|                          |                       |
|--------------------------|-----------------------|
| Application              | Residential           |
| environmental conditions | Indoor                |
| Mounting                 | Recessed              |
| standard                 | CSA,ULCA Title 24,JA8 |