

3M™ Comfort Grip Gloves

Data Sheet

September 2013

Product Description

3M™ Comfort Grip Gloves offer a comfortable alternative to the traditional cotton and leather work glove. The gloves are constructed from a nylon knit material which offers a comfortable, breathable fit and are perfectly suited for applications where hand flexibility and dexterity are needed. The nitrile rubber coated palm provides gripping ability in wet or oily applications. The Comfort Grip Cut Resistant glove is an excellent choice for applications when working with sharp tools or edges.

Agency Approvals & Self Certifications

Standard	Mechanical Risks	Comfort Grip General Use	Comfort Grip Cut Resistant
ANSI 105-2011 ¹	Blade Cut Resistant	Level 1	Level 3
EN 388	Abrasion Resistance	Level 4	Level 4
	Blade Cut Resistant	Level 1	Level 5
	Tear Resistant	Level 2	Level 4
	Puncture Resistance	Level 2	Level 4

Test Methods: ¹ASTM F1790-05

Materials

Comfort Grip General Use	Nitrile Foam / Nylon Fiber
Comfort Grip Cut Resistant	Nitrile Foam/UHMWPE Glass/Nylon Fiber

Note: Gloves may contain ingredients known to be a possible cause of irritation and/or allergic reaction in persons sensitive to such materials. Immediately seek medical advice if an allergic reaction should occur.

Glove Sizing

It is important to order the right size to insure the best protection and most comfortable fit. Sizes are determined by measuring the circumference of the hand with a tape measure in inches just below the knuckles with the hand closed. These measurements will not account for all possible variations in hand size.

Size #	8	9	10
Size	M	L	XL

Care Instructions

Gloves are hand and machine washable. Do not use chlorine or oxygen bleach. Hang glove to dry in shaded area. Performance characteristics may degrade due to laundering.

3M™ Comfort Grip Gloves

Handling & Safety Precautions

Read all Health Hazard, Precautionary and First Aid statements found in the Material Safety Data Sheet (MSDS) and/or product label of chemicals prior to handling or use.

OSHA 29 CFR Part 1910:138 Personal Protective Equipment: Hand Protection, states that employers shall select and require employees to use appropriate hand protection when employees' hands are exposed to hazards and shall base that selection on an evaluation of the performance characteristics of the hand protection relative to the task(s) to be performed and duration of use.

Disposal

After the glove has been used it may be contaminated with infectious or other hazardous materials. Please dispose of according to local regulations.

WARNING! To reduce the risks of electrical shock:

Do not use on live electrical circuits.

To reduce the risks of cut or mechanical impact:

Do not use when there is a risk of entanglement or near moving machinery.

Note: Although the Comfort Grip Cut Resistant Gloves are cut resistant, they are not cut or puncture proof. Do not subject to high-speed or serrated blades.

To reduce the risk of burns:

Do not expose to open flames or sparks. Gloves are not flameproof or fire retardant.

CAUTION! To reduce the risks of cut or mechanical impact:

Discard and replace the gloves if they become damaged in accordance with local work practice or regulations.

Availability

Please contact your local distributor; available from 3M.com/electrical [Where to Buy] or call 1-800-245-3573.

3M is a trademark of 3M Company.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product, which are not contained in 3M's current publications, or any contrary statements contained on your purchase order, shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability

This product will be free from defects in material and manufacture at the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Electrical Markets Division

6801 River Place Blvd.
Austin, TX 78726-9000
800.245.3573
FAX: 800.245.0329
www.3M.com/electrical

Please recycle
© 3M 2013 All rights reserved
78-8141-6408-9 Rev A