



PASS & SEYMOUR®


Extra Duty While-In-Use Covers

Single, Shallow, Deep & Two Gang

WIUCED10L, WIUCED10S,
WIUCED10DL, WIUCED20L

Innovative design in addition to the latest NEC® requirements provides weather protection while-in-use.

Corner hinges allow versatile polycarbonate covers to be installed either vertically or horizontally. They provide generous interior room to accommodate bends in even the heaviest cords. They are lockable to prevent tampering, and deliver excellent weather resistance thanks to neoprene-blend gasketing, a cord flap seal and our exclusive WaterShed™ channel.



FEATURES & BENEFITS

Exclusive cord flap gasket inhibits water splash from driving rain or sprinklers.

Sturdy polycarbonate construction resists impacts and harsh weather.

Patented corner hinge and cord opening allow vertical or horizontal installation.

Exclusive WaterShed™ Channel keeps water moving outside while cord flap keeps the inside dry.

Preapplied gasket easier to install, saves time, won't get lost or damaged.

Paintable, textured finish hides scratches.

Patented trigger latch opens easily with one finger, yet is lockable to prevent tampering.

Sturdy, molded-in hinge withstands hard use.

Installs without removing electrical device, thanks to patented, **keyed mounting holes**.

Roomy interior provides space for plugs and cord bends.

Shallow profile models have 1" shorter top lid than prior models.

The 2014 NEC® Section 406.9(B)(1) requires that an outlet box load installed for this purpose shall be listed and shall be identified as "extra duty."

WIUCED10SC

FIELD USES / VERTICAL MARKETS

- Industrial
- Education
- Retail
- Hospitality/Lodging
- Health Care
- Institutional
- Office
- Education




PASS & SEYMOUR®

Extra Duty White-In-Use Covers Single, Shallow, Deep & Two Gang

TECHNICAL INFORMATION

| Catalog Number | Bottom Color | Top Color | Device Plates Provided | Plate Width |
|--|--------------------------------|---------------------------------|------------------------|-------------|
| Single Gang | | | | |
| WIUCED10GL WIUCED10CL WIUCED10WL | Gray Gray White | Gray Clear White | | 2 3/8" |
| Single Gang Shallow | | | | |
| WIUCED10SG WIUCED10SC WIUCED10SW WIUCED10SB | Gray Gray White White | Gray Clear White Clear | | 2 3/8" |
| Single Gang Deep | | | | |
| WIUCED10DGL WIUCED10DCL WIUCED10DWL | Gray Gray White | Gray Clear White | | 2 3/8" |
| Two Gang | | | | |
| WIUCED20GL WIUCED20CL WIUCED20WL | Gray Gray White | Gray Clear White | | 2" |
| Extra Plate Kits | | | | |
| WIU10PK WIU10PKW | Gray White | | Single Gang Plate Kit | 2 3/8" |
| WIU20PK WIU20PKW | Gray White | | Two Gang Plate Kit | 2" |



Snap-in device plates require no tools to install and won't fall out. See chart for plates provided with each catalog number.

For more information on these and other P&S products refer to our Catalog or visit our web site.

PASS & SEYMOUR®

Extra Duty While-In-Use Covers

Single, Shallow, Deep & Two Gang



DIMENSIONS

3rd Party Compliance

cULus Listed.
Covers conform to NEMA 3R.
Complies with 2014 NEC® Section 406.9(B)(1).

Performance

| | | |
|---------------|------------|------------|
| Environmental | Waterproof | Extra-Duty |
|---------------|------------|------------|


Materials

| | |
|--------------|-------------------------------------|
| Body | Polycarbonate |
| Cover | .125" Polycarbonate |
| Cover Finish | Textured |
| Screws | 302 Stainless Steel |
| Gasket | Closed Cell Foam, Neoprene Blend |
| Insert Plate | Polycarbonate |


Warranty

1 Year


**SINGLE GANG,
SINGLE GANG SHALLOW,
SINGLE GANG DEEP
COVERS**




**SINGLE GANG
COVER**





**SINGLE GANG
SHALLOW
COVER**



**SINGLE GANG
DEEP
COVER**



TWO GANG COVER



ALSO AVAILABLE...

- Plug Load Control Solutions
- Watertight Plugs & Connectors
- Hospital Grade Devices
- Plugtail® Devices
- Surge Protective Devices
- Ground Connectivity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Configurable Solutions

**Electrical Wiring Systems**

P.O. Box 4822
Syracuse, NY 13221-4822
Phone: 1.800.776.4035
www.legrand.us/passandseymour
570 Applewood Crescent
Vaughan, Ontario L4K 4B4
Phone: 905.738.9195
www.legrand.ca



PASS & SEYMOUR®


Extra Duty While-In-Use Covers

Single, Shallow, Deep & Two Gang

WIUCED10L, WIUCED10S,
WIUCED10DL, WIUCED20L

Innovative design in addition to the latest NEC® requirements provides weather protection while-in-use.

Corner hinges allow versatile polycarbonate covers to be installed either vertically or horizontally. They provide generous interior room to accommodate bends in even the heaviest cords. They are lockable to prevent tampering, and deliver excellent weather resistance thanks to neoprene-blend gasketing, a cord flap seal and our exclusive WaterShed™ channel.



FEATURES & BENEFITS

Exclusive cord flap gasket inhibits water splash from driving rain or sprinklers.

Sturdy polycarbonate construction resists impacts and harsh weather.

Patented corner hinge and cord opening allow vertical or horizontal installation.

Exclusive WaterShed™ Channel keeps water moving outside while cord flap keeps the inside dry.

Preapplied gasket easier to install, saves time, won't get lost or damaged.

Paintable, textured finish hides scratches.

Patented trigger latch opens easily with one finger, yet is lockable to prevent tampering.

Sturdy, molded-in hinge withstands hard use.

Installs without removing electrical device, thanks to patented, **keyed mounting holes**.

Roomy interior provides space for plugs and cord bends.

Shallow profile models have 1" shorter top lid than prior models.

The 2014 NEC® Section 406.9(B)(1) requires that an outlet box load installed for this purpose shall be listed and shall be identified as "extra duty."

WIUCED10SC

FIELD USES / VERTICAL MARKETS

- Industrial
- Education
- Retail
- Hospitality/Lodging
- Health Care
- Institutional
- Office
- Education



PASS & SEYMOUR®

Extra Duty White-In-Use Covers Single, Shallow, Deep & Two Gang

TECHNICAL INFORMATION

| Catalog Number | Bottom Color | Top Color | Device Plates Provided | Plate Width |
|--|--------------------------------|---------------------------------|------------------------|-------------|
| Single Gang | | | | |
| WIUCED10GL WIUCED10CL WIUCED10WL | Gray Gray White | Gray Clear White | | 2 3/8" |
| Single Gang Shallow | | | | |
| WIUCED10SG WIUCED10SC WIUCED10SW WIUCED10SB | Gray Gray White White | Gray Clear White Clear | | 2 3/8" |
| Single Gang Deep | | | | |
| WIUCED10DGL WIUCED10DCL WIUCED10DWL | Gray Gray White | Gray Clear White | | 2 3/8" |
| Two Gang | | | | |
| WIUCED20GL WIUCED20CL WIUCED20WL | Gray Gray White | Gray Clear White | | 2" |
| Extra Plate Kits | | | | |
| WIU10PK WIU10PKW | Gray White | | Single Gang Plate Kit | 2 3/8" |
| WIU20PK WIU20PKW | Gray White | | Two Gang Plate Kit | 2" |



Snap-in device plates require no tools to install and won't fall out. See chart for plates provided with each catalog number.

For more information on these and other P&S products refer to our Catalog or visit our web site.

PASS & SEYMOUR®

Extra Duty While-In-Use Covers

Single, Shallow, Deep & Two Gang



DIMENSIONS

3rd Party Compliance

cULus Listed.
Covers conform to NEMA 3R.
Complies with 2014 NEC® Section 406.9(B)(1).

Performance

| | | |
|---------------|------------|------------|
| Environmental | Waterproof | Extra-Duty |
|---------------|------------|------------|


Materials

| | |
|--------------|-------------------------------------|
| Body | Polycarbonate |
| Cover | .125" Polycarbonate |
| Cover Finish | Textured |
| Screws | 302 Stainless Steel |
| Gasket | Closed Cell Foam, Neoprene Blend |
| Insert Plate | Polycarbonate |


Warranty

1 Year


**SINGLE GANG,
SINGLE GANG SHALLOW,
SINGLE GANG DEEP
COVERS**




**SINGLE GANG
COVER**





**SINGLE GANG
SHALLOW
COVER**



**SINGLE GANG
DEEP
COVER**



TWO GANG COVER



ALSO AVAILABLE...

- Plug Load Control Solutions
- Watertight Plugs & Connectors
- Hospital Grade Devices
- Plugtail® Devices
- Surge Protective Devices
- Ground Connectivity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Configurable Solutions

**Electrical Wiring Systems**

P.O. Box 4822
Syracuse, NY 13221-4822
Phone: 1.800.776.4035
www.legrand.us/passandseymour
570 Applewood Crescent
Vaughan, Ontario L4K 4B4
Phone: 905.738.9195
www.legrand.ca