

Glare Free



WATTS: 27

WLSG27LED

CCT: 4500K

LUMENS: 3,017

LPW: 113 CRI: 82

DIMMING: 10-100%

CCT: 3000K

LUMENS: 2,749

LPW: 105 CRI: 81

DIMMING: 10-100%

Patent Pending



Ordering Information


CATALOG #	DESCRIPTION	VOLTS	COLOR TEMP
WLSG27LED	27W LED Wall Light	120-277	4500K
WLSG27LED3K	27W LED Wall Light	120-277	3000K

Options

ADD SUFFIX #	DESCRIPTION
PC	120V Photocontrol
PM	208-277V Photocontrol

Note: Atlas uses only premium LED compatible photocontrols

Recommended Mounting Height - 10-12 ft.



Mtg. Hgt.	90°			45°			Avg. FCs 450 SQ. FT.
	5'	10'	15'	5'	10'	15'	
10'	7.2	3.3	1.8	6.8	4.4	2.3	4.3
12'	5.6	3.0	1.8	5.3	3.7	2.3	3.6



Performance

- Eliminates Glare & Offensive Light
- Less Wasted Light
- More Footcandles on the Ground
- Creates a Smooth & Uniform Light Pattern

Dimensions and Specifications

Overall Height: 8.5"
Overall Width: 8.75"

Depth: 9.05"
Weight: 6.6 lbs.



*The majority of Atlas Lighting Products are assembled in USA facilities by an American Workforce utilizing both Domestic and Foreign components



Glare Free



WATTS: 27

WLSG27LED

CCT: 4500K

LUMENS: 3,017

LpW: 113 CRI: 82

DIMMING: 10-100%

CCT: 3000K

LUMENS: 2,749

LpW: 105 CRI: 81

DIMMING: 10-100%

Patent Pending



Ordering Information


CATALOG #	DESCRIPTION	VOLTS	COLOR TEMP
WLSG27LED	27W LED Wall Light	120-277	4500K
WLSG27LED3K	27W LED Wall Light	120-277	3000K

Options

ADD SUFFIX #	DESCRIPTION
PC	120V Photocontrol
PM	208-277V Photocontrol

Note: Atlas uses only premium LED compatible photocontrols

Recommended Mounting Height - 10-12 ft.





Performance

- Eliminates Glare & Offensive Light
- Less Wasted Light
- More Footcandles on the Ground
- Creates a Smooth & Uniform Light Pattern

Dimensions and Specifications

Overall Height: 8.5"
Overall Width: 8.75"

Depth: 9.05"
Weight: 6.6 lbs.



*The majority of Atlas Lighting Products are assembled in USA facilities by an American Workforce utilizing both Domestic and Foreign components

