




Pass & Seymour

# Weatherproof Boxes & Covers Boxes Single & Two Gang

WPB23, WPB33, WPB232, WPB332

**Rugged construction for any wet location, with appropriate cover.**

**W**e finish these durable, cast aluminum boxes with a tough, baked-on, electrostatic polyester powder coat for excellent resistance to scratches and corrosion. They are ideal for wet and/or damp locations with appropriate cover. All ship with two closure plugs and mounting lugs.




## Features & Benefits

**Heavy die-cast aluminum.**

**Available in standard and deep configurations.**

**Available in 1/2" and 3/4" hub sizes, from 3 to 6 hole configurations.**



WPB332

**Baked-on, electrostatic polyester powder paint** for superior scratch- and corrosion-resistant finish.

**UL Listed**, for wet and/or damp locations with appropriate cover.

**Simply strike desired knockout studs with a sharp hammer blow** for clean mounting holes.

## Field Uses/Vertical Markets





- Industrial
- Health Care
- Education
- Institutional
- Retail
- Office
- Hospitality/Lodging
- Multiple Dwelling

# Weatherproof Boxes & Covers

## Boxes

### Single & Two Gang

#### Ordering Information

Catalog Number	Description	Color
<b>Single Gang</b>		
 <b>WPB23</b> <b>WPB23-BR</b> <b>WPB23-W</b>	3 Hole 1/2", 18.5 Cu. In. (1 Hole Each End, 1 Hole in Back)	Gray Bronze White
 <b>WPB33</b> <b>WPB33-BR</b> <b>WPB33-W</b>	3 Hole 3/4", 18.5 Cu. In. (1 Hole Each End, 1 Hole in Back)	Gray Bronze White
<b>Two Gang</b>		
 <b>WPB232</b> <b>WPB232-W</b>	3 Hole 1/2", 30.5 Cu. In. (1 Hole Each End, 1 Hole in Back)	Gray White
 <b>WPB332</b>	3 Hole 3/4", 30.5 Cu. In. (1 Hole Each End, 1 Hole in Back)	Gray

For more information on these and other P&S products refer to our Product Guide or visit our web site.

# Weatherproof Boxes & Covers

## Boxes

### Single & Two Gang



Pass & Seymour

#### Technical Specifications


3rd Party Compliance	
UL Listed.	
CSA Certified.	

Performance	
Environmental	Weatherproof


Materials	
Body	Cast Aluminum
Screws	Steel, Zinc-Plated
Finish	Baked-On, Electrostatic Polyester Powder Coat

**Warranty**

1 Year




Dimensions for Single Gang Box



Dimensions for Two Gang Box

## Complementary Devices & Accessories




### WEATHERPROOF BOXES & COVERS

- While-In-Use Covers
- Heavy Cast Aluminum Covers
- Cast Covers




### WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers



### SWITCHES

- Heavy-Duty Toggle
- Heavy-Duty Lighted Toggle
- Heavy-Duty Security
- Heavy-Duty Locking
- Construction Grade Toggle
- Commercial Grade Toggle



### STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Construction Grade
- Commercial Grade



### GFCIs

- Construction Grade with Auto-Ground
- Construction Grade
- Construction Grade Dead Front

## Also available...

- Light Almond Devices
- Decorator Devices
- Hospital Grade Devices
- PlugTail™ Devices
- TVSS & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Configurable Solutions



**Legrand/Pass & Seymour**  
P.O. Box 4822  
Syracuse, NY 13221-4822  
800-223-4185

**North America Headquarters**  
60 Woodlawn Street  
West Hartford, CT 06110  
Phone: 1.877.BY.LEGRAND (295.3472)  
Fax: 1.860.232.2062  
www.legrand.us

**Legrand Canada**  
570 Applewood Crescent  
Vaughan, ON, L4K 4B4  
Phone: 905.738.9195  
Fax: 905.738.9721  
www.legrand.ca




Pass & Seymour

# Weatherproof Boxes & Covers Boxes Single & Two Gang

WPB23, WPB33, WPB232, WPB332

**Rugged construction for any wet location, with appropriate cover.**

**W**e finish these durable, cast aluminum boxes with a tough, baked-on, electrostatic polyester powder coat for excellent resistance to scratches and corrosion. They are ideal for wet and/or damp locations with appropriate cover. All ship with two closure plugs and mounting lugs.




## Features & Benefits

**Heavy die-cast aluminum.**

**Available in standard and deep configurations.**

**Available in 1/2" and 3/4" hub sizes, from 3 to 6 hole configurations.**



WPB332

**Baked-on, electrostatic polyester powder paint** for superior scratch- and corrosion-resistant finish.

**UL Listed,** for wet and/or damp locations with appropriate cover.

**Simply strike desired knockout studs with a sharp hammer blow** for clean mounting holes.

## Field Uses/Vertical Markets





- Industrial
- Health Care
- Education
- Institutional
- Retail
- Office
- Hospitality/Lodging
- Multiple Dwelling

# Weatherproof Boxes & Covers

## Boxes

### Single & Two Gang

#### Ordering Information

Catalog Number	Description	Color
<b>Single Gang</b>		
 <b>WPB23</b> <b>WPB23-BR</b> <b>WPB23-W</b>	3 Hole 1/2", 18.5 Cu. In. (1 Hole Each End, 1 Hole in Back)	Gray Bronze White
 <b>WPB33</b> <b>WPB33-BR</b> <b>WPB33-W</b>	3 Hole 3/4", 18.5 Cu. In. (1 Hole Each End, 1 Hole in Back)	Gray Bronze White
<b>Two Gang</b>		
 <b>WPB232</b> <b>WPB232-W</b>	3 Hole 1/2", 30.5 Cu. In. (1 Hole Each End, 1 Hole in Back)	Gray White
 <b>WPB332</b>	3 Hole 3/4", 30.5 Cu. In. (1 Hole Each End, 1 Hole in Back)	Gray

For more information on these and other P&S products refer to our Product Guide or visit our web site.

# Weatherproof Boxes & Covers

## Boxes

### Single & Two Gang



Pass & Seymour

#### Technical Specifications


3rd Party Compliance	
UL Listed.	
CSA Certified.	

Performance	
Environmental	Weatherproof


Materials	
Body	Cast Aluminum
Screws	Steel, Zinc-Plated
Finish	Baked-On, Electrostatic Polyester Powder Coat

**Warranty**

1 Year




Dimensions for Single Gang Box



Dimensions for Two Gang Box

## Complementary Devices & Accessories




### WEATHERPROOF BOXES & COVERS

- While-In-Use Covers
- Heavy Cast Aluminum Covers
- Cast Covers




### WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers



### SWITCHES

- Heavy-Duty Toggle
- Heavy-Duty Lighted Toggle
- Heavy-Duty Security
- Heavy-Duty Locking
- Construction Grade Toggle
- Commercial Grade Toggle



### STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Construction Grade
- Commercial Grade



### GFCIs

- Construction Grade with Auto-Ground
- Construction Grade
- Construction Grade Dead Front

## Also available...

- Light Almond Devices
- Decorator Devices
- Hospital Grade Devices
- PlugTail™ Devices
- TVSS & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Configurable Solutions



**Legrand/Pass & Seymour**  
P.O. Box 4822  
Syracuse, NY 13221-4822  
800-223-4185

**North America Headquarters**  
60 Woodlawn Street  
West Hartford, CT 06110  
Phone: 1.877.BY.LEGRAND (295.3472)  
Fax: 1.860.232.2062  
www.legrand.us

**Legrand Canada**  
570 Applewood Crescent  
Vaughan, ON, L4K 4B4  
Phone: 905.738.9195  
Fax: 905.738.9721  
www.legrand.ca