

# Specifications

Photo is representative

## Eaton WPMV7L-UNV1

Eaton Crouse-Hinds series Champ WPMV LED wall pack, 0.21A, Cool white, Dimmable driver, 3/4" entry, 150-175W equiv, 50/60 Hz, Tempered glass lens, 7000 lm, 115 lm/W, Die cast alum, Yoke mt, 7x6 distribution, 120-277 Vac, 125-250 Vdc, 59W

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Champ WPMV LED wall pack light fixture
<b>CATALOG NUMBER</b>	WPMV7L-UNV1
<b>UPC</b>	662276892910
<b>PRODUCT LENGTH/DEPTH</b>	9.16 in
<b>PRODUCT HEIGHT</b>	12.76 in
<b>PRODUCT WIDTH</b>	12.6 in
<b>PRODUCT WEIGHT</b>	14 lb
<b>PRODUCT TYPE</b>	LED wall pack light fixture



Powering Business Worldwide

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	4X
<b>INGRESS PROTECTION (IP) RATINGS</b>	IP66

## Product specifications

<b>LAMP TYPE</b>	LED
<b>LUMENS</b>	7000
<b>LUMENS PER WATT</b>	115
<b>COLOR TEMPERATURE</b>	Cool white
<b>OPTICAL DISTRIBUTION</b>	7x6
<b>MOUNTING METHOD</b>	Yoke
<b>VOLTAGE RATING</b>	120-277 Vac, 125-250 Vdc
<b>FREQUENCY RATING</b>	50/60 Hz
<b>LENS MATERIAL</b>	Tempered glass
<b>WATTAGE</b>	59 W
<b>AMPERAGE RATING</b>	0.21 A
<b>POWER FACTOR</b>	> 0.90
<b>DIMMING</b>	Dimmable driver
<b>ENTRY SIZE</b>	3/4"
<b>MATERIAL</b>	Die cast aluminum
<b>EQUIVALENT LUMINAIRE</b>	150-175W

## Resources

3D MODELS	<a href="#">SP3D Design Package - Champ Pro WPMV LED Industrial Wallpack Light Fixtures</a>
BROCHURES	<a href="#">Crouse-Hinds series industrial LED lighting solutions</a> <a href="#">Crouse-Hinds series WPMV LED brochure</a> <a href="#">Crouse-Hinds series Global LED lighting portfolio</a>
CATALOGS	<a href="#">Crouse-Hinds series Champ WPMV LED catalog page</a>
INSTALLATION INSTRUCTIONS	<a href="#">IF 1893 - Champ-Pak WPMVL LED Wall Pack</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - WPMV7L-UNV1</a> <a href="#">Crouse-Hinds series Champ WPMV LED IES photometric files</a>

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

