



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WR279 3/0 to 3/0 H Tap Conn

Abb Installation Products, Inc

| | |
|------------------|--|
| Catalog Number | WR279 |
| Manufacturer | Abb Installation Products, Inc |
| Description | H-Type Compression Connector, Non-Insulated, Aluminum Conductor Material, 2 Conductors, Up to 90 °C Operating Temperature, 1-13/16 In Overall Length, Compression/Crimp Terminal, 0.15 LB/Ea |
| Weight per unit | 0.1450 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|----------------------|--|
| connection | Compression |
| insulation | None |
| Material | Aluminum |
| Number of Conductors | 2 |
| Wire Size | Main: 2/0 to #1 ACSR or 3/0 to 1/0 STR or 4/0 to 2/0 SOL AWG , Tap: 2/0 to #1 ACSR or 3/0 to 1/0 STR or 3/0 to 2/0 SOL AWG |

Dimensions and Weight

| | |
|------|---------------------|
| Size | Length 1-13/16 inch |
|------|---------------------|

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | 3/0 TO 3/0 H TAP CONN |
| extra long description | ABB WR279 AL HTYPE COMPCONN 2/0-1AC |

Manufacturer Information

| | |
|-------|----------------------|
| Brand | Blackburn Mechanical |
| GTIN | 00783786100071 |
| UPC | 783786100071 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------------|
| Category Description | T&B C TAP LUGS |
| Type | H-Type Compression Tap Connector |

Packaging

| | |
|-----------------|-------|
| Carton | 25 |
| Package | 250 |
| Weight Per each | 0.145 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| Application | For Combinations of Aluminum to Aluminum and Aluminum to Copper Conductors |
| environmental conditions | All Seasons / Conditions |
| Mounting | None |
| standard | RUS Accepted. Complies with ANSI C119.4 Specifications |
| Temperature Rating | up to 90 C |