



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WWCGB Gry Winged Wire Conn

*Nsi Industries*

|                  |   |
|------------------|---|
| Catalog Number   | WWCGB   |
| Manufacturer     | Nsi Industries  |
| Description      | The Easy-Twist WWC-G-B 250-Count Bag Of Grey Winged Wire Connectors Are Designed For Use On Copper Wires In The 18-8 Awg Size Range. Theyâ€™re Made Of Flame-Retardant Thermoplastic Rated For A Maximum Temperature Of 105Ëš Celsius (221Ëš Fahrenheit). The Quick-Grip Square Spring Design Grips In Fewer Twists and Can Dead-End A Single Wire, While The Ergonomic Swept-Back Wing Design and Ribbed Texture Makes Them Easy to Twist. Their Compact Design Is Useful For Applications In Tight Areas or Anywhere Else You |
| Weight per unit  | 2.8 (lbs/each)  |
| Product Category | Electrical Fixture Conn ( Nuts  |

### Features

|                      |               |
|----------------------|---------------|
| Material             | Thermoplastic |
| Number of Conductors | 1             |
| Voltage Rating       | 600           |
| Warranty             | 1 YEAR        |
| Wire Type            | CU Wire Only  |

### Material, Color, and Finish

|        |               |
|--------|---------------|
| Color  | Gray          |
| Finish | Thermoplastic |

### Dimensions and Weight

|      |                           |
|------|---------------------------|
| Size | H=1.31 - W=1.00 - ID=.394 |
|------|---------------------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | GRY WINGED WIRE CONN  |
| extra long description | NSI WWC-G-B Easy-Twist Winged Red -   |
| Features               | Connecting wires is faster and easier than ever with the professional performance features of Easy-Twist wire connectors from NSI. These connectors feature a specialized design to install in half the time of a typical wire connector, saving you time and energy. The conical screw shape grips in fewer twists and the outside of the connector is textured with easy-grip ribs for comfortable twisting. The expert team at NSI designed these connectors with key convenience and performance features for electrical in |
| Long Description       | The Easy-Twist WWC-G-B 250-Count Bag of Grey Winged Wire Connectors are designed for use on copper wires in the 18-8 AWG size range. They are made of flame-retardant thermoplastic rated for a maximum temperature of 105°C (221°F Fahrenheit). The quick-grip square spring design grips in fewer twists and can dead-end a single wire, while the ergonomic swept-back wing design and ribbed texture makes them easy to twist. Their compact design is useful for applications in tight areas or anywhere else you          |
| Product Type           | Easy-Twist Winged Red - STD Jar   |
| Special Features       | Winged Grey Wire Connector - 100 Pcs Bag  |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | NSI            |
| GTIN                      | 00662381141408 |
| Manufacturers Part Number | WWC-G-B        |
| UPC                       | 662381141408   |

## Taxonomies, Classifications, and Categories

|                      |                        |
|----------------------|------------------------|
| Category Description | WIRE NUTS              |
| Type                 | Winged Wire Connectors |

## Availability

|             |     |
|-------------|-----|
| minimum qty | 250 |
|-------------|-----|

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 250 |
| Weight Per each | 2.8 |

## Uses, Certifications, and Standards

|                          |               |
|--------------------------|---------------|
| Application              | Splicing Wire |
| environmental conditions | 105 C         |
| standard                 | UL 486C       |
| Temperature Rating       | 105 C         |