



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



X17SA KLRK X17SA 1/2 Hub Alum Cond Body

Hubbell--Killark

| | |
|------------------|---|
| Catalog Number | X17SA |
| Manufacturer | Hubbell--Killark |
| Description | 1/2" X Hub, Aluminum Form 7 Conduit Body, |
| Weight per unit | 2.8 (lbs/each) |
| Product Category | Alum |

Features

| | |
|------|--------|
| Form | Form 7 |
|------|--------|

Material, Color, and Finish

| | |
|--------|--------------------|
| Color | Gray |
| Finish | Powder Epoxy Paint |

Dimensions and Weight

| | |
|----------|------|
| Height | 2 |
| Hub Size | 1/2" |
| Length | 6 |
| Width | 4 |

Descriptions

| | |
|------------------------|---|
| Description | KLRK X17SA 1/2 HUB ALUM COND BODY |
| extra long description | KLRK X17SA 1/2" ALUM COND BODY "X" |
| Long Description | 1/2" X Hub, Aluminum Form 7 Conduit Body, |
| Product Type | 1/2" Alum Cond Body "X" |
| Special Features | Intermateability UL Listed and CSA Certified interchangeability with competitive products. Suitable for wet locations when used with gaskets. Innovative spring clip design for installation ease and repeat usage. Smooth integral wire bushings protects cabl |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | KILLARK |
| GTIN | 00783936080581 |
| Manufacturers Part Number | X17SA |
| series | Duraloy 7 |
| UPC | 783936080581 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | FORM 7, 8, CONDULETS, COVERS, & GASKETS |
| Type | Conduit Body |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Package | 5 |
| Weight Per each | 2.8 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

To provide access to conductors for pulling, splicing, and maintenance. Threaded for rigid conduit and IMC.

standard

UL, CSA