

Eaton XBUT4D22

Catalog Number: XBUT4D22

Eaton XB IEC terminal block, Screw Connection Multi-Conductor Terminal Blocks, Gray, 10 AWG/4 mm² maximum wire, Four-wire

General specifications



Product Name	Catalog Number
Eaton XB IEC terminal block	XBUT4D22
UPC	Product Length/Depth
782116905188	1.85 in
Product Height	Product Width
2.17 in	0.24 in
Product Weight	Warranty
0.04 lb	1 year
Certifications	
UL Listed	
CSA Certified	

Product specifications

Type

IEC-XB Series

Amperage Rating

36A (IEC), 30A (UL)

Voltage rating

IEC 500V, UL 150V

Resources

Brochures

[XB IEC TERMINAL BLOCKS](#)

[XB IEC terminal blocks—versatility, quality, and reliability](#)

Specifications and datasheets

[Eaton Specification Sheet - XBUT4D22](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton XBUT4D22

Catalog Number: XBUT4D22

Eaton XB IEC terminal block, Screw Connection Multi-Conductor Terminal Blocks, Gray, 10 AWG/4 mm² maximum wire, Four-wire

General specifications



Product Name	Catalog Number
Eaton XB IEC terminal block	XBUT4D22
UPC	Product Length/Depth
782116905188	1.85 in
Product Height	Product Width
2.17 in	0.24 in
Product Weight	Warranty
0.04 lb	1 year
Certifications	
UL Listed	
CSA Certified	

Product specifications

Type

IEC-XB Series

Amperage Rating

36A (IEC), 30A (UL)

Voltage rating

IEC 500V, UL 150V

Resources

Brochures

[XB IEC TERMINAL BLOCKS](#)

[XB IEC terminal blocks—versatility, quality, and reliability](#)

Specifications and datasheets

[Eaton Specification Sheet - XBUT4D22](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)