

# Eaton XBUT35

Catalog Number: XBUT35

Eaton XB IEC terminal block, 16 mm Screw connection single level-through-feed, Gray, 8 AWG/6 mm<sup>2</sup> maximum wire, IEC 800V, EN 700V, UL 600V, IEC #24-8 AWG, EN #24-8 AWG, UL #24-8 AWG wire, IEC 57A, EN 40,50A, UL 50A



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton XB IEC terminal block	XBUT35
<b>UPC</b>	<b>Product Length/Depth</b>
782116905065	2.37 in
<b>Product Height</b>	<b>Product Width</b>
2.88 in	0.63 in
<b>Product Weight</b>	<b>Warranty</b>
0.02 lb	1 year
<b>Certifications</b>	
CSA Certified	
UL Listed	

## Product specifications

### Type

IEC-XB Series

### Amperage Rating

527 (IEC), 40A (EN), 50A (EN), 50A (UL)

### Voltage rating

IEC 800V, EN 700V, UL 600V

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - XBUT35](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton XBUT35

Catalog Number: XBUT35

Eaton XB IEC terminal block, 16 mm Screw connection single level-through-feed, Gray, 8 AWG/6 mm<sup>2</sup> maximum wire, IEC 800V, EN 700V, UL 600V, IEC #24-8 AWG, EN #24-8 AWG, UL #24-8 AWG wire, IEC 57A, EN 40,50A, UL 50A



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton XB IEC terminal block	XBUT35
<b>UPC</b>	<b>Product Length/Depth</b>
782116905065	2.37 in
<b>Product Height</b>	<b>Product Width</b>
2.88 in	0.63 in
<b>Product Weight</b>	<b>Warranty</b>
0.02 lb	1 year
<b>Certifications</b>	
CSA Certified	
UL Listed	

## Product specifications

### Type

IEC-XB Series

### Amperage Rating

527 (IEC), 40A (EN), 50A (EN), 50A (UL)

### Voltage rating

IEC 800V, EN 700V, UL 600V

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - XBUT35](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)