

# Eaton XTOE020CCSS

Catalog Number: XTOE020CCSS

Eaton C440 electronic overload relay, XT Electronic Overload Relay - IEC, 4-20A, Selectable 10A, Class 10, 20, 30, 45mm frame

## General specifications



Photo is representative

### Product Name

Eaton C440 electronic overload relay

### Catalog Number

XTOE020CCSS

### UPC

786685412481

### Product Length/Depth

4.32 in

### Product Height

6.5 in

### Product Width

1.8 in

### Product Weight

0.87 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

CE Marked

### Certifications

CSA Certified

UL Listed

## Product specifications

### Overload range

4-20A

### Type

Electronic overload relay

### Frame size

45 mm

### Mounting method

Separate

### Trip type

Selectable 10 A, class 10 ,20, 30

## Resources

### Brochures

[C440 Electronic Overload Relay](#)

### Specifications and datasheets

[Eaton Specification Sheet - XTOE020CCSS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton XTOE020CCSS

Catalog Number: XTOE020CCSS

Eaton C440 electronic overload relay, XT Electronic Overload Relay - IEC, 4-20A, Selectable 10A, Class 10, 20, 30, 45mm frame

## General specifications



Photo is representative

### Product Name

Eaton C440 electronic overload relay

### Catalog Number

XTOE020CCSS

### UPC

786685412481

### Product Length/Depth

4.32 in

### Product Height

6.5 in

### Product Width

1.8 in

### Product Weight

0.87 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

CE Marked

### Certifications

CSA Certified

UL Listed

## Product specifications

### Overload range

4-20A

### Type

Electronic overload relay

### Frame size

45 mm

### Mounting method

Separate

### Trip type

Selectable 10 A, class 10 ,20, 30

## Resources

### Brochures

[C440 Electronic Overload Relay](#)

### Specifications and datasheets

[Eaton Specification Sheet - XTOE020CCSS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)