

Eaton XTOE045DCS

Catalog Number: XTOE045DCS

Eaton C440 electronic overload relay, XT IEC Electronic Overload Relay, 9-45A overload range, 55 mm Frame size, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type



General specifications

| | |
|--------------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton C440 electronic overload relay | XTOE045DCS |
| UPC | Product Length/Depth |
| 786685416533 | 1.8 in |
| Product Height | Product Width |
| 4.3 in | 1.42 in |
| Product Weight | Compliances |
| 0.87 lb | ATEX Compliant |
| | RoHS Compliant |
| | CE Marked |

Certifications

UL Listed
IEC 60947
CSA Certified
EN 60947

Product specifications

Overload range

9-45A

Type

Electronic overload relay

Frame size

55 mm

Mounting method

Direct

Contact configuration

NO, NC

Trip type

Selectable 10 A, class 10 ,20, 30

Resources

Brochures

[C440 Electronic Overload Relay](#)

Specifications and datasheets

[Eaton Specification Sheet - XTOE045DCS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton XTOE045DCS

Catalog Number: XTOE045DCS

Eaton C440 electronic overload relay, XT IEC Electronic Overload Relay, 9-45A overload range, 55 mm Frame size, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type



General specifications

| | |
|--------------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton C440 electronic overload relay | XTOE045DCS |
| UPC | Product Length/Depth |
| 786685416533 | 1.8 in |
| Product Height | Product Width |
| 4.3 in | 1.42 in |
| Product Weight | Compliances |
| 0.87 lb | ATEX Compliant |
| | RoHS Compliant |
| | CE Marked |

Certifications

UL Listed
IEC 60947
CSA Certified
EN 60947

Product specifications

Overload range

9-45A

Type

Electronic overload relay

Frame size

55 mm

Mounting method

Direct

Contact configuration

NO, NC

Trip type

Selectable 10 A, class 10 ,20, 30

Resources

Brochures

[C440 Electronic Overload Relay](#)

Specifications and datasheets

[Eaton Specification Sheet - XTOE045DCS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)