

Eaton XTOE100GCS

Catalog Number: XTOE100GCS

Eaton C440 electronic overload relay, XT IEC Electronic Overload Relay, 20-100A overload range, 105 mm Frame size, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type

General specifications

Product Name	Catalog Number
Eaton C440 electronic overload relay	XTOE100GCS
UPC	Product Length/Depth
786685416571	7.5 in
Product Height	Product Width
6.5 in	3.253 in
Product Weight	Compliances
0.87 lb	CE Marked
	RoHS Compliant
	ATEX Compliant

Certifications

UL Listed
CSA Certified
IEC 60947
EN 60947



Product specifications

Overload range

20-100A

Type

Electronic overload relay

Frame size

105 mm

Mounting method

Direct

Contact configuration

NO, NC

Trip type

Selectable 10 A, class 10 ,20, 30

Resources

Brochures

[C440 Electronic Overload Relay](#)

Drawings

[XTOE100G_S AutoCAD 2D Footprint \(mm\)](#)

[XTOE100G_S AutoCAD 2D Footprint](#)

[XTOE100G_S 2D PDF](#)

[XTOE100G_S 3D Model Xchange](#)

[XTOE100G_S 2D Drawing Xchange](#)

[XTOE100G_S 3D Inventor](#)

Installation instructions

[XTOE/ZEB IEC Electronic Overload - Self Powered](#)

Specifications and datasheets

[Eaton Specification Sheet - XTOE100GCS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton XTOE100GCS

Catalog Number: XTOE100GCS

Eaton C440 electronic overload relay, XT IEC Electronic Overload Relay, 20-100A overload range, 105 mm Frame size, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type

General specifications

Product Name	Catalog Number
Eaton C440 electronic overload relay	XTOE100GCS
UPC	Product Length/Depth
786685416571	7.5 in
Product Height	Product Width
6.5 in	3.253 in
Product Weight	Compliances
0.87 lb	CE Marked
	RoHS Compliant
	ATEX Compliant

Certifications

UL Listed
CSA Certified
IEC 60947
EN 60947



Product specifications

Overload range

20-100A

Type

Electronic overload relay

Frame size

105 mm

Mounting method

Direct

Contact configuration

NO, NC

Trip type

Selectable 10 A, class 10 ,20, 30

Resources

Brochures

[C440 Electronic Overload Relay](#)

Drawings

[XTOE100G_S AutoCAD 2D Footprint \(mm\)](#)

[XTOE100G_S AutoCAD 2D Footprint](#)

[XTOE100G_S 2D PDF](#)

[XTOE100G_S 3D Model Xchange](#)

[XTOE100G_S 2D Drawing Xchange](#)

[XTOE100G_S 3D Inventor](#)

Installation instructions

[XTOE/ZEB IEC Electronic Overload - Self Powered](#)

Specifications and datasheets

[Eaton Specification Sheet - XTOE100GCS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)