

# Specifications



Photo is representative



## Eaton XTCE095FS1A

Eaton XT IEC contactor, 95A, Side-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 95A, Frame F, 90 mm, 50-60 Hz, 40, 50, 100, 125 hp (3PH @200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing contactor

### General specifications

<b>PRODUCT NAME</b>	Eaton XT IEC contactor
---------------------	------------------------

<b>CATALOG NUMBER</b>	XTCE095FS1A
-----------------------	-------------

<b>UPC</b>	786685365145
------------	--------------

<b>PRODUCT LENGTH/DEPTH</b>	1 in
-----------------------------	------

<b>PRODUCT HEIGHT</b>	1 in
-----------------------	------

<b>PRODUCT WIDTH</b>	1 in
----------------------	------

<b>PRODUCT WEIGHT</b>	1 lb
-----------------------	------

<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
-----------------	--

<b>CERTIFICATIONS</b>	UL Listed CSA Certified EN 60947 IEC 60947
-----------------------	---

## Product specifications

AMPERAGE RATING	95A
HP RATING - MAX	40, 50, 100, 125 hp (3PH @200,230,460,575 V)
NUMBER OF POLES	Three-pole
TYPE	Full voltage non-reversing contactor
FREQUENCY RATING	50-60 Hz
FRAME SIZE	90 mm
TERMINALS	Screw terminals
COIL	110-120 Vac, 50/60 Hz
COIL VOLTAGE	110-120 Vac, 50/60 Hz
CONTACT CONFIGURATION	1 NO, 1 NC
CONTINUOUS AMPERE RATING	95 A
SERIES	XT IEC
OPERATION	Non-reversing

## Resources

CATALOGS	<a href="#">Motor Control and Protection, IEC Contactors and Starters, Volume 5, Tab 1</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - XTCE095FS1A</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

