



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YA34N 500 Cop *Burndy LLC*

Catalog Number	YA34N
Manufacturer	Burndy LLC
Description	500 Kcmil Cu, One Hole, 1/2 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, UL/Csa, 90 C, Up to 35KV, Brown Color Code, 20 or 299 Die Index.
Weight per unit	0.4600 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	20
Material	Copper
pallet quantity	3700
Voltage Rating	35

Material, Color, and Finish

Color Code	BROWN
------------	-------

Descriptions

Description	500 COP
extra long description	BUR YA34N 500 CU 1-HOLE LONG 1/2
Long Description	500 kcmil CU, One Hole, 1/2 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kv,BROWN Color Code, 20 or 299 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Die Index: 20 Or 299, Finish: Electro-Tin Plated, Wire Strip Length: 2-5/16 IN, Tongue Angle: Straight, Temperature Rating: 90 DEG C, Color Code: Brown, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W34VT Die, (4), Hydraulic: BCT500HS, Y500CTHS Tool, W34VT, W34RT Die, (4), Y35, Y39, Y750, PAT750 Tool, U34RT, U31ART Die, (4), Y46 Tool, U34RT, U31ART Die With PUADP-1 Adapter, (

Manufacturer Information

Brand	BURNDY
GTIN	00781810017937
Manufacturers Part Number	YA34N
UPC	781810017937

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel, Tin Plated



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.46

Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B