

**BURNDY Catalog Number**  
**UPC Number**

YAV26L  
7818100256977

**Description**

2/0 HVYDTY RING 3/8 STUD, Index  
No:44

**Status**

Active

**Web Use**

BURNDY Product Line

**Dimensional**

Tongue Angle	Straight
Strip Length	13/16
Length (in)	2.31
Tongue Type	Ring
Pad Width (in)	0.93

**General**

Product Description	Copper Compression Lug, 1 Hole w/ Inspection Window, AN-2/0 Flex, 3/8" Stud, Short Barrel, Tin Plated
---------------------	--

**Conductor(s)**

Aircraft Cable Size (Range)	AN 00
Copper Solid Size (Range)	N/A
Navy Cable Size (Range)	N/A
Copper Stranded (Range)	2/0 AWG

**Physical**

Type of Plating	Tin
Connector Type	Terminal
Plated (Yes or No)	Y

**Approvals / Certifications**

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
Mil-Spec Class Code	Class 1
CULUS	N
Industry Standards	UL467, Military Specified (Mil-Spec)

**Documentation**

For further technical assistance, please contact us


**BURNDY LLC - USA**

47 East Industrial Park Drive  
Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175



**BURNDY Catalog Number**  
**UPC Number**

YAV26L  
7818100256977

**Description**

2/0 HVYDTY RING 3/8 STUD, Index  
No:44

**Status**

Active

**Web Use**

BURNDY Product Line

**Dimensional**

Tongue Angle	Straight
Strip Length	13/16
Length (in)	2.31
Tongue Type	Ring
Pad Width (in)	0.93

**General**

Product Description	Copper Compression Lug, 1 Hole w/ Inspection Window, AN-2/0 Flex, 3/8" Stud, Short Barrel, Tin Plated
---------------------	--

**Conductor(s)**

Aircraft Cable Size (Range)	AN 00
Copper Solid Size (Range)	N/A
Navy Cable Size (Range)	N/A
Copper Stranded (Range)	2/0 AWG

**Physical**

Type of Plating	Tin
Connector Type	Terminal
Plated (Yes or No)	Y

**Approvals / Certifications**

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
Mil-Spec Class Code	Class 1
CULUS	N
Industry Standards	UL467, Military Specified (Mil-Spec)

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175