



BURNDY Catalog Number
UPC Number

YAV4CL
7818108071944
4AWG HVYDTY RING 1/4
STU,1.37 IN L
Active

Description
Status

Web Use
BURNDY Product Line

Tongue Angle
Strip Length
Length (in)
Tongue Type
Pad Width (in)

Dimensional
Straight
1/2
1.37
Ring
0.55

Product Description

General
Copper Compression Lug, Ring
Tongue, 1 Hole w/ Inspection
Hole, AN-4 Flex, 1/4" Stud, Short
Barrel, Electro-Tin Plated

Aircraft Cable Size (Range)
Copper Solid Size (Range)
Navy Cable Size (Range)
Copper Stranded (Range)

Conductor(s)
AN 4
N/A
N/A
4

Type of Plating
Connector Type
Plated (Yes or No)

Physical
Tin - Electro Plated
Terminal
Y

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
Mil-Spec Class Code
CULUS

Approvals / Certifications

Y
Y
Compliant
N
Class 1
N
UL467, Military Specified (Mil-Spec)

Industry Standards

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175



BURNDY Catalog Number
UPC Number

YAV4CL
7818108071944
4AWG HVYDTY RING 1/4
STU,1.37 IN L
Active

Description
Status

Web Use
BURNDY Product Line

Tongue Angle
Strip Length
Length (in)
Tongue Type
Pad Width (in)

Dimensional
Straight
1/2
1.37
Ring
0.55

Product Description

General
Copper Compression Lug, Ring
Tongue, 1 Hole w/ Inspection
Hole, AN-4 Flex, 1/4" Stud, Short
Barrel, Electro-Tin Plated

Aircraft Cable Size (Range)
Copper Solid Size (Range)
Navy Cable Size (Range)
Copper Stranded (Range)

Conductor(s)
AN 4
N/A
N/A
4

Type of Plating
Connector Type
Plated (Yes or No)

Physical
Tin - Electro Plated
Terminal
Y

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
Mil-Spec Class Code
CULUS

Approvals / Certifications

Y
Y
Compliant
N
Class 1
N
UL467, Military Specified (Mil-Spec)

Industry Standards

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175