

INSULATED WIRE STRIPPER/CUTTER

**10-18 Solid AWG &
12-20 Stranded AWG**



 1000 V

KLEIN-KURVE®

**KLEIN
TOOLS®**

KLEIN-KURVE® Insulated Wire Stripper/Cutter

KLEIN TOOLS
For Professionals... Since 1857®

Insulated Wire Stripper/Cutter for Both Solid and Stranded!

Introducing the first insulated Klein Kurve® Wire Stripper/Cutter – a multiple function insulated tool that can cut, strip, loop and gauge both 10-18 solid and 12-20 stranded AWG wire, plus cleanly shear 6-32 and 8-32 screws. The 11055-INS features curved handles with comfortable orange grips consisting of two layers of insulation to protect against electric shock, and integral guards to prevent hand contact with conductive parts. Klein insulated tools meet or exceed the ASTM F1505-01, IEC 60900:2004 standards for insulated tools, and they comply with NFPA-70E, 2004 ed. They are clearly marked with the official 1000-volt rating symbol.

Features

Strips 10-18 solid and 12-20 stranded AWG wire.

Comfortable, curved handles.

Hardened steel with precision ground stripping holes for easy removal of insulation.

Holes for looping and bending.

Easy to read markings on both sides.

Strong gripping serrated nose for easy bending, shaping and pulling of wire.

Black-oxide finish resists corrosion.

Precision shear-type blades for clean cuts on solid and stranded copper wire.

Do NOT use to cut steel wire.

Spring-loaded action for self-opening.

Thick, exceptionally tough, high-dielectric white inner coating is bonded to the tool.

Flame retardant, impact resistant, bright orange outer coating.

Integral guards help prevent hand contact with conductive parts.

11055-INS



Cleanly Shears 6-32 and 8-32 Screws

Thread screw into proper hole to desired length and squeeze handles to shear.



1000 V

Tool meets or exceeds ASTM F1505-01, IEC 60900:2004 and complies with NFPA-70E, 2004 ed. standards.

Ordering Information

Cat. No.	UPC No. 0-92644+	Description	Strips and Cuts	Overall Length	Weight (lbs.)
NEW! 11055-INS	74068-8	Insulated Wire Stripper/Cutter	10 – 18 AWG solid 12 – 20 AWG stranded	8" (203 mm)	.75

Also Available

11049-INS	74067-1	Insulated Wire Stripper/Cutter	8 – 16 AWG stranded (6.0 – 1.0 mm ²)	7" (178 mm)	.70
11045-INS	74049-7	Insulated Wire Stripper/Cutter	10 – 18 AWG solid (4.0 – .75 mm ²)	7" (178 mm)	.70

▲WARNING: Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.

▲WARNING: Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

▲WARNING: Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.

▲WARNING: Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

▲WARNING: Because moisture, films, or other surface contaminants are conductive, Klein insulated tools must be kept clean, dry, and free of any surface contaminants.

