


# Saws & Blades

Saws and blades from Klein are designed with the professional user in mind, providing superior results with less effort.

For Professionals...  
Since 1857™



# Saws & Blades

## High-Tension Hack Saw

- Adjustable blade tension up to 30,000 PSI for fast, precise cuts.
- Soft-touch grips.
- Alternative 45 degree mounting for flush cutting.
- Front mount for reciprocating saw blades.
- Blade storage in handle.
- Includes 12" x 24 TPI bi-metal hack saw blade and 6" x 24 TPI bi-metal reciprocating saw blade.



702-12

Cat. No.	Blade Length	Overall Length	Weight (lbs.)
702-12	12" (305 mm)	16-1/4" (413 mm)	1.45

## Dual-Purpose Hacksaw – Golden Tri-Cut™ 3-in-1 Blade

- Blade has three teeth sizes.
- Blade converts quickly to 90° or 45° for standard or flush-cut applications.
- Pivot-lock adjusts blade tension for straighter cuts and longer blade life.
- Set screw allows for storage of extra blades and secures blade for “jab” sawing.
- Aluminum finger grip handle and front end.
- Thumb guard for two-hand sawing.



Blade has three teeth sizes

701-S

Cat. No.	Blade Length	Overall Length	Weight (lbs.)
701-S	12" (305 mm)	16" (406 mm)	1.45

## Bi-Metal Blades

1224BI

- Special high-speed steel teeth fused to regular carbon-steel body, which provides superior cutting and longer life.
- Withstands greater saw tension for less blade flexing.
- Fits all 12" (305 mm) hacksaw blades.
- Blue finish.
- Available in box of 100 blades or in a reclosable, heavy-vinyl, seal-tight pouch of ten blades.

Cat. No.	Pack Size	Teeth Per Inch	Length	Weight Per Pack (lbs.)
1218BI-P	10-pack	18	12" (305 mm)	.45
1224BI-P	10-pack	24	12" (305 mm)	.45
1232BI-P	10-pack	32	12" (305 mm)	.45
1218BI	100-pack	18	12" (305 mm)	4.50
1224BI	100-pack	24	12" (305 mm)	4.50
1232BI	100-pack	32	12" (305 mm)	4.50

## Golden Tri-Cut™ Blades

1200BI



Blade has three teeth sizes

- Unique design provides three teeth sizes on one blade.
- Has 32 teeth/inch up front for quick starts, 24 teeth/inch in the middle and 18 teeth/inch on the end for fast and smooth conventional cutting.
- Special high-speed steel teeth fused to carbon-steel provide superior cutting action and long life.
- Gold finish.
- Available in box of 100 blades or reclosable, heavy-vinyl, seal-tight pouch of ten blades.


Cat. No.	Pack Size	Teeth Per Inch	Length	Weight Per Pack (lbs.)
1200BI-P	10-pack	32-24-18	12" (305 mm)	.45
1200BI	100-pack	32-24-18	12" (305 mm)	4.50

All dimensions are in inches and (millimeters).



[www.kleintools.com](http://www.kleintools.com)

See page 3?? for additional information on warnings.



# Saws & Blades

## Job Saw

- Cuts drywall, wallboard, plywood and plastic.
- Triple ground teeth for a fast cut.
- Blade cuts in both directions (push and pull).
- Hardened, carbon-steel blade for durability.
- Hardened, beveled blade point for scoring and plunge cuts.
- Comfort cushion grip with thumb groove.
- Handle structure designed for strength and durability.
- Flat-end grip for palming or punching through drywall.



725



Cat. No.	Blade Length	Overall Length	Weight (lbs.)
725	6" (152 mm)	12" (305 mm)	.31

## Magic-Slot Compass Saws

- Magic-Slot design allows fast blade changing without removing thumbscrew.
- Handle is strong, lightweight, die-cast zinc with blue finish.
- Handle is contoured for comfort.
- Blade is tough, high-quality carbon steel, 8" (203 mm) long, with ten teeth per inch for general-purpose use.
- Replacement blades and handle can be ordered separately.



703

Cat. No.	Description	Overall Length	Teeth Per Inch	Weight (lbs.)
703	Magic-Slot compass saw complete with Cat. No. 706 blade	13" (330 mm)	10	1.20
702	Magic-Slot compass saw handle only. Takes only Magic-Slot cut-in or general-purpose blades.	5" (127 mm)	—	1.10

## Compass Saw Blades

- For cutting through wallboard or Masonite to install wiring, outlet boxes, etc.
- Tough high-quality carbon steel.
- Pointed starter tip.
- Fits Magic-Slot compass saw handle Cat. No. 702.



709

Cat. No.	Blade Length	Teeth Per Inch	Weight (lbs.)
<b>Magic-Slot Electrician's Cut-in Blade</b>			
709	4" (102 mm)	10	.06
<b>General-Purpose Compass Saw Blades</b>			
704	12" (305 mm)	8	.14
705	12" (305 mm)	10	.14
706	8" (203 mm)	10	.09
707	10" (254 mm)	10	.12

All dimensions are in inches and (millimeters).



[www.kleintools.com](http://www.kleintools.com)

See page 3?? for additional information on warnings.

# Reciprocating Saw Blades

## Premium Reciprocating Saw Blades

- Heavy duty, bi-metal blades are 1" wide and .042 thick, which offers greater rigidity for smooth, straight, accurate cuts.
- Innovative tooth geometry and blade design for faster cutting, less vibration and longer blade life.
- Available in blade lengths of 6", 9" and 12" to meet a variety of cutting applications.
- 1/2" universal shank to fit all popular reciprocating saw tools.



31810

Cat. No.	Blade Length	TPI	Blade Width	Blade Thickness	Pack	Main Applications
31810	6"	10	1"	0.042	5	HD - Metal
31802	6"	14	1"	0.042	5	HD - Metals 1/8" thick & above
31804	6"	18	1"	0.042	5	HD - Metals 18 ga. to 1/8"
31806	6"	24	1"	0.042	5	HD - Metals 18 ga. & under
31808	9"	10	1"	0.042	5	HD - Metal
31832	9"	14	1"	0.042	5	HD - Metals 1/8" thick & above
31834	9"	18	1"	0.042	5	HD - Metals 18 ga. to 1/8"
31836	12"	10	1"	0.042	5	HD - Metal
31838	12"	14	1"	0.042	5	HD - Metals 1/8" thick & above
31840	12"	18	1"	0.042	5	HD - Metals 18 ga. to 1/8"

## Reciprocating Saw Blades

- Bi-metal blades in a variety of blade lengths and thicknesses for different cutting applications.
- Shock resistant teeth resist strippage.
- 1/2" universal shank to fit all popular reciprocating saw tools.




31750



31722

Cat. No.	Blade Length	TPI	Blade Width	Blade Thickness	Pack	Main Applications
31710	6"	6	3/4"	0.035	5	Wood with nails
31710-15	6"	6	3/4"	0.035	15	Wood with nails
31714	6"	6	3/4"	0.035	5	Plaster
31716	6"	6	3/4"	0.050	5	Wood with nails
31716-15	6"	6	3/4"	0.050	15	Wood with nails
31720	6"	10	3/4"	0.035	5	Wood, plastic and non-ferrous
31722	6"	14	3/4"	0.035	5	Heavy ga. metals
31722-15	6"	14	3/4"	0.035	15	Heavy ga. metals
31722-50	6"	14	3/4"	0.035	50	Heavy ga. metals
31728	6"	18	3/4"	0.035	5	Heavy ga. metals
31728-15	6"	18	3/4"	0.035	15	Heavy ga. metals
31728-50	6"	18	3/4"	0.035	50	Heavy ga. metals
31734	6"	24	3/4"	0.035	5	18 ga. and under
31734-15	6"	24	3/4"	0.035	15	18 ga. and under

Cat. No.	Blade Length	TPI	Blade Width	Blade Thickness	Pack	Main Applications
31738	8"	10/14	3/4"	0.035	5	Wood with nails
31738-15	8"	10/14	3/4"	0.035	15	Wood with nails
31742	8"	14	3/4"	0.035	5	Heavy ga. metals
31742-15	8"	14	3/4"	0.035	15	Heavy ga. metals
31746	8"	18	3/4"	0.035	5	Heavy ga. metals
31746-15	8"	18	3/4"	0.035	15	Heavy ga. metals
31750	9"	6	3/4"	0.050	5	Wood with nails
31750-15	9"	6	3/4"	0.050	15	Wood with nails
31754	9"	6	7/8"	0.062	3	Demo
31756	9"	10	7/8"	0.062	3	Demo
31758	12"	6	3/4"	0.050	5	Wood with nails
31758-15	12"	6	3/4"	0.050	15	Wood with nails
31762	12"	6	7/8"	0.062	3	Demo
31764	12"	10	7/8"	0.062	3	Demo
31766	12"	10/14	3/4"	0.050	5	Wood with nails



All dimensions are in inches and (millimeters).



**NOTE:** Read and follow safety instructions in power tool owner's manual.

[www.kleintools.com](http://www.kleintools.com)

See page ??? for additional information on warnings.