



1. Identification

1. Identification			
Product identifier	RTV Silicone Adhesive & Sealant - White (p	pressurized)	
Other means of identification			
Product code	No. 14056 (Item# 1004790)		
Recommended use	Sealant and adhesive		
Recommended restrictions	None known.		
Manufacturer/Importer/Supplier/	Distributor information		
Manufactured or sold by:			
Company name	CRC Industries, Inc.		
Address	885 Louis Dr.		
	Warminster, PA 18974 US		
Telephone			
General Information	215-674-4300		
Technical Assistance	800-521-3168		
Customer Service	800-272-4620		
24-Hour Emergency	800-424-9300 (US)		
(CHEMTREC)	703-527-3887 (International)		
Website	www.crcindustries.com		
2. Hazard(s) identification			
Physical hazards	Gases under pressure	Compressed gas	
Health hazards	Not classified.		
Environmental hazards	Hazardous to the aquatic environment, acute hazard	Category 3	
	Hazardous to the aquatic environment, long-term hazard	Category 3	
OSHA defined hazards	Not classified.		
Label elements			
	\bigwedge		
Signal word	Warning		
Hazard statement	Contains gas under pressure; may explode if heated. Harmful to aquatic life with long lasting effects.		
Precautionary statement			
Prevention	Do not puncture or incinerate container. Do not expose to heat or store at temperatures above 49°C/120°F. Use with adequate ventilation. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying. Avoid release to the environment.		
Response	Wash hands after handling.		
Storage	-	d place. Exposure to high temperature may cause	
Disposal	Dispose of contents/container in accordance v	vith local/regional/national regulations.	
Hazard(s) not otherwise classified (HNOC)	None known.		
Supplemental information			

When heated to temperature above 300°F/150°C in the presence of air, product may form formaldehyde vapors. When exposed to water or humid air, product evolves acetic acid (HOAc).

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
polydimethylsiloxane, hydroxy-terminated		70131-67-8	70 - 90
amorphous silica		7631-86-9	5 - 10
distillates (petroleum), hydrotreated middle		64742-46-7	5 - 10
aluminum		7429-90-5	1 - 3
titanium dioxide		13463-67-7	1 - 3
carbon black		1333-86-4	< 1

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

	5	
4. First-aid measures		
Inhalation	Move to fresh air. Get medical attention if symptoms occur.	
Skin contact	Wash with water and soap as a precaution. Get medical attention if symptoms occur.	
Eye contact	Flush eyes with water as a precaution. If eye irritation persists: Get medical advice/attention.	
Ingestion	If swallowed, do NOT induce vomiting. Get medical attention if symptoms occur. Rinse mouth thoroughly.	
Most important symptoms/effects, acute and delayed	Direct contact with eyes may cause temporary irritation.	
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically.	
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.	
5. Fire-fighting measures		
Suitable extinguishing media	Water. Alcohol resistant foam. Dry chemical powder. Carbon dioxide (CO2).	
Unsuitable extinguishing media	None known.	
Specific hazards arising from the chemical	During fire, gases hazardous to health may be formed.	
Special protective equipment and precautions for firefighters	Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.	
Fire-fighting equipment/instructions	In case of fire: Stop leak if safe to do so. Move containers from fire area if you can do so without risk. Cool containers exposed to heat with water spray and remove container, if no risk is involved	
General fire hazards	Contents under pressure. Pressurized container may rupture when exposed to heat or flame.	
6. Accidental release mea	isures	
Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Keep our low areas. Many gases are heavier than air and will spread along ground and collect in low or confined areas (sewers, basements, tanks). Wear appropriate protective equipment and clothin during clean-up. Emergency personnel need self-contained breathing equipment. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ventilat closed spaces before entering them. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.	
Methods and materials for containment and cleaning up	Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material. Prevent product from entering drains. Stop the flow of material, if this is without risk. For waste disposal, see section 13 of the SDS.	
Environmental precautions	Avoid release to the environment. Inform appropriate managerial or supervisory personnel of all environmental releases. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground	

drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling	Pressurized container: Do not pierce or burn, even after use. Do not use if spray button is missing or defective. Do not spray on a naked flame or any other incandescent material. Do not smoke while using or until sprayed surface is thoroughly dry. Do not cut, weld, solder, drill, grind, or expose containers to heat, flame, sparks, or other sources of ignition. Use caution around energized equipment. The metal container will conduct electricity if it contacts a live source. This may result in injury to the user from electrical shock and/or flash fire. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Avoid release to the environment. Observe good industrial hygiene practices. For product usage instructions, see the product label.
Conditions for safe storage, including any incompatibilities	Level 1 Aerosol.
	Contents under pressure. Do not expose to heat or store at temperatures above 120°F/49°C as can may burst. Do not puncture, incinerate or crush. Do not handle or store near an open flame, heat or other sources of ignition. Store in a well-ventilated place. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection

Occupational exposure limits

The following constituents are the only constituents of the product which have a PEL, TLV or other recommended exposure limit. At this time, the other constituents have no known exposure limits.

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Туре	Value	Form
aluminum (CAS 7429-90-5)	PEL	5 mg/m3	Respirable fraction.
		15 mg/m3	Total dust.
carbon black (CAS 1333-86-4)	PEL	3.5 mg/m3	
distillates (petroleum), hydrotreated middle (CAS 64742-46-7)	PEL	5 mg/m3	Mist.
,		400 mg/m3	
		100 ppm	
titanium dioxide (CAS 13463-67-7)	PEL	15 mg/m3	Total dust.
US. OSHA Table Z-3 (29 CFR 1910.100	0)		
Components	Туре	Value	Form
aluminum (CAS 7429-90-5)	TWA	5 mg/m3	Respirable fraction.
		15 mg/m3	Total dust.
		50 mppcf	Total dust.
		15 mppcf	Respirable fraction.
amorphous silica (CAS 7631-86-9)	TWA	0.8 mg/m3	
,		20 mppcf	
titanium dioxide (CAS 13463-67-7)	TWA	5 mg/m3	Respirable fraction.
		15 mg/m3	Total dust.
		50 mppcf	Total dust.
		15 mppcf	Respirable fraction.
US. ACGIH Threshold Limit Values			_
Components	Туре	Value	Form
aluminum (CAS 7429-90-5)	TWA	1 mg/m3	Respirable fraction.
carbon black (CAS 1333-86-4)	TWA	3 mg/m3	Inhalable fraction.
distillates (petroleum), hydrotreated middle (CAS 64742-46-7)	TWA	5 mg/m3	Inhalable fraction.
titanium dioxide (CAS 13463-67-7)	TWA	10 mg/m3	
US. NIOSH: Pocket Guide to Chemical			
Components	Туре	Value	Form
aluminum (CAS 7429-90-5)	TWA	5 mg/m3	Welding fume or pyrophoric powder.

US. NIOSH: Pocket Guide to Chemical Hazards Components Type

Components	Туре	Value	Form
		5 mg/m3	Respirable.
		10 mg/m3	Total
amorphous silica (CAS 7631-86-9)	TWA	6 mg/m3	
carbon black (CAS 1333-86-4)	TWA	0.1 mg/m3	
distillates (petroleum), hydrotreated middle (CAS 64742-46-7)	STEL	10 mg/m3	Mist.
,	TWA	5 mg/m3	Mist.
Biological limit values	No biological exposure limits noted for the	ne ingredient(s).	
Exposure guidelines	Occupational Exposure Limits are not re	levant to the current physic	al form of the product.
Appropriate engineering controls	Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Provide eyewash station.		
Individual protection measures	, such as personal protective equipment	t	
Eye/face protection	Wear safety glasses with side shields (o	r goggles).	
Skin protection Hand protection	Wear protective gloves such as: Nitrile. I	Butyl rubber.	
Other	Wear appropriate chemical resistant clothing.		
Respiratory protection	If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.		
Thermal hazards	Wear appropriate thermal protective clothing, when necessary.		
General hygiene considerations	Observe any medical surveillance requirements. When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants. Contaminated work clothing should not be allowed out of the workplace.		

9. Physical and chemical properties

Appearance	
Physical state	Solid, Liquid.
Form	Paste.
Color	White.
Odor	Acetic acid.
Odor threshold	Not available.
рН	Not available.
Melting point/freezing point	Not available.
Initial boiling point and boiling range	680 °F (360 °C) estimated
Flash point	> 212 °F (> 100 °C) Closed Cup
Evaporation rate	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or exp	losive limits
Flammability limit - lower (%)	Not available.
Flammability limit - upper (%)	Not available.
Vapor pressure	95440.2 hPa estimated
Vapor density	Not available.
Relative density	1.01

Solubility (water)	Not available.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	500 °F (260 °C) estimated
Decomposition temperature	Not available.
Viscosity (kinematic)	Not available.
Percent volatile	< 3 %

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Heat, flames and sparks. Contact with incompatible materials. When heated to temperature above 300°F/150°C in the presence of air, product may form formaldehyde vapors. When exposed to water or humid air, product evolves acetic acid (HOAc).
Incompatible materials	Strong oxidizing agents. Water, moisture.
Hazardous decomposition products	Carbon oxides. Silicone dioxide. Formaldehyde. Metal oxides. Nitrogen oxides (NOx).

11. Toxicological information

Information on likely routes of exposure			
Inhalation	Prolonged inhalation may be harmful.		
Skin contact	Prolonged skin contact may cause temporary irritation.		
Eye contact	Direct contact with eyes may cause temporary irritation	on.	
Ingestion	Health injuries are not known or expected under norr	nal use.	
Symptoms related to the physical, chemical and toxicological characteristics	Direct contact with eyes may cause temporary irritation.		
Information on toxicological effe	cts		
Acute toxicity	Not known.		
Components	Species	Test Results	
amorphous silica (CAS 7631-86-9)			
<u>Acute</u>			
Oral			
LD50	Rat	> 22500 mg/kg	
carbon black (CAS 1333-86-4)			
Acute			
Oral			
LD50	Rat	> 8000 mg/kg	
titanium dioxide (CAS 13463-67-7)			
Acute			
Dermal		40000	
LD50	Rabbit	> 10000 mg/kg	
Oral		10000 #	
LD50	Rat	> 10000 mg/kg	
* Estimates for product may be based on additional component data not shown.			
* Estimates for product may be	based on additional component data not shown.		
* Estimates for product may be Skin corrosion/irritation	e based on additional component data not shown. Prolonged skin contact may cause temporary irritatio	n.	
•	-		
Skin corrosion/irritation Serious eye damage/eye	Prolonged skin contact may cause temporary irritatio		

Germ cell mutagenicity		ailable to indicate product or any compor or genotoxic.	nents present at greater than 0.1% are
Carcinogenicity	This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.		
IARC Monographs. Overall	Evaluation of	Carcinogenicity	
amorphous silica (CAS 7 OSHA Specifically Regulate Not regulated. US. National Toxicology Pr Not listed.	ed Substance	s (29 CFR 1910.1001-1050)	to carcinogenicity to humans.
Reproductive toxicity	This produc	t is not expected to cause reproductive	or developmental effects.
Specific target organ toxicity - single exposure	Not classifie	ed.	
Specific target organ toxicity - repeated exposure	Not classifie	ed.	
Aspiration hazard	Not an aspi	ration hazard.	
Chronic effects	Prolonged e	exposure may cause chronic effects.	
12. Ecological informatio	n		
Ecotoxicity	Harmful to a	aquatic life with long lasting effects.	
Components		Species	Test Results
aluminum (CAS 7429-90-5)			
Aquatic			
Fish	LC50	Rainbow trout,donaldson trout (Oncorhynchus mykiss)	0.16 mg/l, 96 hours
distillates (petroleum), hydrot	reated middle	(CAS 64742-46-7)	
Aquatic Crustacea	EC50	Water flea (Daphnia pulex)	2.7 - 5.1 mg/l, 48 hours
Fish	LC50	Rainbow trout,donaldson trout (Oncorhynchus mykiss)	8.8 mg/l, 96 hours
			8.8 mg/l, 96 hours
titanium dioxide (CAS 13463-	-67-7)		
Aquatic			
Crustacea	EC50	Water flea (Daphnia magna)	> 1000 mg/l, 48 hours
Acute			
Fish	LC50	Fathead minnow (Pimephales prome	elas) 1000 mg/l, 96 hours
* Estimates for product may b Persistence and degradability	be based on a	dditional component data not shown.	
Bioaccumulative potential			
Bioconcentration factor (Be	CF)	352	
Mobility in soil	No data ava	ailable.	
Other adverse effects	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.		
13. Disposal consideration	ons		
Disposal of waste from residues / unused products	This product is not a RCRA hazardous waste (See 40 CFR Part 261.20 – 261.33). Empty containers may be recycled. Consult authorities before disposal. Contents under pressure. Do not puncture, incinerate or crush. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose in accordance with all applicable regulations.		
Hazardous waste code	Not regulate	ed.	
Contaminated packaging		Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers may retain product residue, follow label warnings even after container is	

14. Transport information

DOT	
UN number	UN1950
UN proper shipping name	Aerosols, non-flammable, Limited Quantity
Transport hazard class(es)	
Class	2.2
Subsidiary risk	-
Label(s)	2.2
Packing group	Not applicable.
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Packaging exceptions	306
Packaging non bulk	None
Packaging bulk	None
ΙΑΤΑ	
UN number	UN1950
UN proper shipping name	Aerosols, non-flammable, Limited Quantity
Transport hazard class(es)	
Class	2.2
Subsidiary risk	-
Packing group	Not applicable.
ERG Code	2L
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Other information	
Passenger and cargo aircraft	Allowed with restrictions.
Cargo aircraft only	Allowed with restrictions.
IMDG	
UN number	UN1950
UN proper shipping name	AEROSOLS, Limited Quantity
Transport hazard class(es)	
Class	2.2
Subsidiary risk	-
Packing group	Not applicable.
Environmental hazards	
Marine pollutant	No.
EmS	Not available.
•	Read safety instructions, SDS and emergency procedures before handling.

15. Regulatory information

This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

US federal regulations

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

```
Not regulated.
```

US EPCRA (SARA Title III) Section 313 - Toxic Chemical: Listed substance

Not listed.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

CERCLA Hazardous Substances: Reportable quantity

Not listed.

Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section	112(r) Accidental Release Prevention (40 CFR 68.130)	
Not regulated.		
Safe Drinking Water Act (SDWA)	Not regulated.	
Food and Drug Administration (FDA)	Not regulated.	
Superfund Amendments and Section 311/312 Hazard categories	I Reauthorization Act of 1986 (SARA) Immediate Hazard - No Delayed Hazard - No Fire Hazard - No Pressure Hazard - Yes Reactivity Hazard - No	
SARA 302 Extremely hazardous substance	No	
S state regulations		
US. California. Candidate Ch (a))	emicals List. Safer Consumer Products Regulations (Cal. Code Regs	, tit. 22, 69502.3, subd.
titanium dioxide (CAS 134	36-4) Irotreated middle (CAS 64742-46-7)	
aluminum (CAS 7429-90- carbon black (CAS 1333- titanium dioxide (CAS 134	36-4) 63-67-7)	
US. Massachusetts RTK - Su aluminum (CAS 7429-90-		
amorphous silica (CAS 76 carbon black (CAS 1333- titanium dioxide (CAS 134	31-86-9) 36-4) 63-67-7)	
•	d Community Right-to-Know Law	
titanium dioxide (CAS 134	31-86-9) 36-4) Irotreated middle (CAS 64742-46-7)	
US. Rhode Island RTK		
aluminum (CAS 7429-90- carbon black (CAS 1333- titanium dioxide (CAS 134	36-4)	
US. California Proposition 6 California Safe Drinking V any chemicals currently list	5 /ater and Toxic Enforcement Act of 1986 (Proposition 65): This material is sted as carcinogens or reproductive toxins.	not known to contain
olatile organic compounds (VO EPA	C) regulations	
VOC content (40 CFR 51.100(s))	< 3 %	
Consumer products (40 CFR 59, Subpt. C)	Not regulated	
State		
Consumer products	This product is regulated as a Sealant and Caulking Compound. This product is compliant for use in all 50 states.	
VOC content (CA)	< 3 %	
VOC content (OTC)	< 3 %	
ternational Inventories		
Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	Yes
Canada	Domestic Substances List (DSL)	Yes

Country(s) or region	Inventory name	On inventory (yes/no)*
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	Yes
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s) A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date	08-15-2017
Prepared by	Allison Yoon
Version #	01
Further information	Not available.
HMIS® ratings	Health: 1 Flammability: 1 Physical hazard: 0 Personal protection: B
NFPA ratings	Health: 1 Flammability: 1 Instability: 0
NFPA ratings	
Disclaimer	The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC's knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries, Inc
Revision Information	This document has undergone significant changes and should be reviewed in its entirety.