



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 13104RS1030 13104RQD07 With Two Near-Range Photodiodes

Eaton Corp

Catalog Number	13104RS1030
Manufacturer	Eaton Corp
Description	Eaton Comet 18MM Tubular Photoelectric Sensor, Right Angle, Sensor Dist 2 In., 100 Ma PNP, 250 Ma NPN Max DC, NPN/PNP Open Collector, 100 Ma PNP, 250 Ma NPN At 10-30 VDC, 4 Pin M12 Connector, 10-30 VDC Input, Background Suppression
Weight per unit	1,313.0 (lbs/each)
Product Category	Photoelectric Sensors

### Features

connection	Connector Connector M12
------------	-------------------------

### Dimensions and Weight

Height	3.02
Length	0.6
Width	0.71

### Descriptions

Description	13104RQD07 WITH TWO NEAR-RANGE PHOTODIODES
extra long description	ETN 13104RS1030 13104RQD07 W/TWO NE
Features	Eaton's Comet Series Photoelectric Sensors is a complete line of high performance, 18 mm tubular sensors with a variety of models and modes to solve virtually any sensing problem.
Long Description	Eaton Comet 18mm tubular photoelectric sensor, Right Angle, Sensor dist 2 In., 100 mA PNP, 250 mA NPN max DC, NPN/PNP Open Collector, 100 mA PNP, 250 mA NPN at 10-30 Vdc, 4 Pin M12 Connector, 10-30 Vdc input, Background Suppression
Product Type	13104RQD07 W/Two Near-Range Photodiodes

### Manufacturer Information

Brand	Eaton
GTIN	00782114981405
Manufacturers Part Number	13104RS1030
UPC	782114981405

### Taxonomies, Classifications, and Categories

Category Description	PROXIMITY SWITCHES AND CORDSETS
Type	Tubular photoelectric sensor

### Packaging

Carton	1
Weight Per each	1313



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application .....	Vehicles: On-Road - PickUp & Delivery: Food .....
Operating Temperature .....	-40° to 158°F (-40° to 70°C) .....
standard .....	Contact Manufacturer .....