



SAFETY DATA SHEET

1. Identification

Product identifier	Citrus Degreaser - 15 oz
Other means of identification	
Product Code	No. 14170 (Item# 1004861)
Recommended use	General purpose degreaser
Recommended restrictions	None known.
Manufacturer/Importer/Supplier/Distributor information	
Manufactured or sold by:	
Company name	CRC Industries, Inc.
Address	885 Louis Dr. Warminster, PA 18974 US
Telephone	
General Information	215-674-4300
Technical Assistance	800-521-3168
Customer Service	800-272-4620
24-Hour Emergency (CHEMTREC)	800-424-9300 (US)
Website	www.crcindustries.com

2. Hazard(s) identification

Physical hazards	Flammable aerosols Gases under pressure	Category 1 Compressed gas
Health hazards	Skin corrosion/irritation Serious eye damage/eye irritation Sensitization, skin Aspiration hazard	Category 2 Category 2A Category 1 Category 1
Environmental hazards	Hazardous to the aquatic environment, acute hazard Hazardous to the aquatic environment, long-term hazard	Category 2 Category 2
OSHA defined hazards	Not classified.	

Label elements



Signal word	Danger
Hazard statement	Extremely flammable aerosol. Contains gas under pressure; may explode if heated. May be fatal if swallowed and enters airways. Causes skin irritation. May cause an allergic skin reaction. Causes serious eye irritation.
Precautionary statement	
Prevention	Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use. Do not apply while equipment is energized. Extinguish all flames, pilot lights, and heaters. Vapors will accumulate readily and may ignite. Use only with adequate ventilation; maintain ventilation during use and until all vapors are gone. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying. If you experience any symptoms listed on this label, increase ventilation or leave the area. Avoid breathing mist/vapors. Wash thoroughly after handling. Contaminated work clothing must not be allowed out of the workplace. Wear eye protection/face protection. Wear protective gloves.

Response	If swallowed: Immediately call a poison center/doctor. Do NOT induce vomiting. If on skin: Wash with plenty of water. If skin irritation or rash occurs: Get medical advice/attention. Take off contaminated clothing and wash it before reuse. If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
Storage	Store in a well-ventilated place. Store locked up. Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. Exposure to high temperature may cause can to burst.
Disposal	Dispose of contents/container in accordance with local/regional/national/international regulations.
Hazard(s) not otherwise classified (HNOC)	None known.
Supplemental information	None.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
distillates (petroleum), hydrotreated light		64742-47-8	70 - 80
d-limonene		5989-27-5	5 - 10
orange, sweet, ext.		8028-48-6	3 - 5
carbon dioxide		124-38-9	1 - 3
turpentine		9005-90-7	< 2

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	Move to fresh air. Call a physician if symptoms develop or persist.
Skin contact	Remove contaminated clothing immediately and wash skin with soap and water. In case of eczema or other skin disorders: Seek medical attention and take along these instructions. Wash contaminated clothing before reuse.
Eye contact	Immediately flush eyes with plenty of water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Get medical attention if irritation develops and persists.
Ingestion	Call a physician or poison control center immediately. Rinse mouth. Do not induce vomiting. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs.
Most important symptoms/effects, acute and delayed	Aspiration may cause pulmonary edema and pneumonitis. Headache. Nausea, vomiting. Diarrhea. Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Skin irritation. May cause redness and pain. May cause an allergic skin reaction. Dermatitis. Rash.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves. Wash contaminated clothing before reuse.

5. Fire-fighting measures

Suitable extinguishing media	Water fog. Alcohol resistant foam. Dry chemical powder. Dry chemicals. Carbon dioxide (CO ₂).
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	Contents under pressure. Pressurized container may rupture when exposed to heat or flame. During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.
Fire-fighting equipment/instructions	In case of fire: Stop leak if safe to do so. Move containers from fire area if you can do so without risk. Cool containers exposed to heat with water spray and remove container, if no risk is involved. Containers should be cooled with water to prevent vapor pressure build up. Use standard firefighting procedures and consider the hazards of other involved materials. In the event of fire and/or explosion do not breathe fumes.
General fire hazards	Extremely flammable aerosol. Contents under pressure. Pressurized container may rupture when exposed to heat or flame. Will burn if involved in a fire.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Keep out of low areas. Many gases are heavier than air and will spread along ground and collect in low or confined areas (sewers, basements, tanks). Wear appropriate protective equipment and clothing during clean-up. Avoid breathing mist/vapors. Emergency personnel need self-contained breathing equipment. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ventilate closed spaces before entering them. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.

Methods and materials for containment and cleaning up

Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material. This product is miscible in water. Prevent product from entering drains. Stop the flow of material, if this is without risk. Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination. For waste disposal, see section 13 of the SDS.

Environmental precautions

Avoid release to the environment. Inform appropriate managerial or supervisory personnel of all environmental releases. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling

Pressurized container: Do not pierce or burn, even after use. Do not use if spray button is missing or defective. Do not spray on a naked flame or any other incandescent material. Do not smoke while using or until sprayed surface is thoroughly dry. Do not cut, weld, solder, drill, grind, or expose containers to heat, flame, sparks, or other sources of ignition. Use caution around energized equipment. The metal container will conduct electricity if it contacts a live source. This may result in injury to the user from electrical shock and/or flash fire. Avoid breathing mist/vapors. Avoid contact with eyes, skin, and clothing. Avoid prolonged or repeated contact with skin. Avoid prolonged exposure. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Wash hands thoroughly after handling. Avoid release to the environment. Observe good industrial hygiene practices. For product usage instructions, see the product label.

Conditions for safe storage, including any incompatibilities

Level 3 Aerosol.

Pressurized container. Protect from sunlight and do not expose to temperatures exceeding 50°C/122 °F. Do not puncture, incinerate or crush. Do not handle or store near an open flame, heat or other sources of ignition. This material can accumulate static charge which may cause spark and become an ignition source. Store in tightly closed container. Store in a well-ventilated place. Stored containers should be periodically checked for general condition and leakage. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection

Occupational exposure limits

The following constituents are the only constituents of the product which have a PEL, TLV or other recommended exposure limit. At this time, the other constituents have no known exposure limits.

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value
carbon dioxide (CAS 124-38-9)	PEL	9000 mg/m ³
		5000 ppm

US. ACGIH Threshold Limit Values

Components	Type	Value
carbon dioxide (CAS 124-38-9)	STEL	30000 ppm
	TWA	5000 ppm

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
carbon dioxide (CAS 124-38-9)	STEL	54000 mg/m ³
		30000 ppm
	TWA	9000 mg/m ³ 5000 ppm

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
distillates (petroleum), hydrotreated light (CAS 64742-47-8)	TWA	100 mg/m ³

US. Workplace Environmental Exposure Level (WEEL) Guides

Components	Type	Value
d-limonene (CAS 5989-27-5)	TWA	165.5 mg/m ³ 30 ppm

Biological limit values	No biological exposure limits noted for the ingredient(s).
Appropriate engineering controls	Good general ventilation should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Provide eyewash station and safety shower.
Individual protection measures, such as personal protective equipment	
Eye/face protection	Wear safety glasses with side shields (or goggles).
Skin protection	
Hand protection	Wear protective gloves such as: Neoprene. Nitrile.
Other	Wear appropriate chemical resistant clothing. Use of an impervious apron is recommended.
Respiratory protection	If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.
Thermal hazards	Wear appropriate thermal protective clothing, when necessary.
General hygiene considerations	When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants. Contaminated work clothing should not be allowed out of the workplace.

9. Physical and chemical properties**Appearance**

Physical state	Liquid.
Form	Aerosol.
Color	Water-white.
Odor	Citrus.
Odor threshold	Not available.
pH	Not available.
Melting point/freezing point	-139.9 °F (-95.5 °C) estimated
Initial boiling point and boiling range	294.8 °F (146 °C) estimated
Flash point	170.0 °F (76.7 °C) Setflash
Evaporation rate	Slow.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	0.5 % estimated
Flammability limit - upper (%)	5.5 % estimated
Vapor pressure	1610 hPa estimated
Vapor density	> 1 (air = 1)
Relative density	0.83

Solubility(ies)	
Solubility (water)	Negligible.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	428 °F (220 °C) estimated
Decomposition temperature	Not available.
Viscosity	Not available.
Percent volatile	97.5 % estimated

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Heat, flames and sparks. Avoid temperatures exceeding the flash point. Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents.
Hazardous decomposition products	Carbon oxides.

11. Toxicological information

Information on likely routes of exposure

Inhalation	Prolonged inhalation may be harmful.
Skin contact	Causes skin irritation. May cause an allergic skin reaction.
Eye contact	Causes serious eye irritation.
Ingestion	Droplets of the product aspirated into the lungs through ingestion or vomiting may cause a serious chemical pneumonia.

Symptoms related to the physical, chemical and toxicological characteristics Aspiration may cause pulmonary edema and pneumonitis. Headache. Nausea, vomiting. Diarrhea. Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Skin irritation. May cause redness and pain. May cause an allergic skin reaction. Dermatitis. Rash.

Information on toxicological effects

Acute toxicity May be fatal if swallowed and enters airways.

Components	Species	Test Results
------------	---------	--------------

distillates (petroleum), hydrotreated light (CAS 64742-47-8)

Acute

Dermal

LD50	Rabbit	> 2000 mg/kg
------	--------	--------------

Inhalation

LC50	Rat	> 5 mg/l, 4 hours
------	-----	-------------------

Oral

LD50	Rat	> 5000 mg/kg
------	-----	--------------

orange, sweet, ext. (CAS 8028-48-6)

Acute

Dermal

LD50	Rabbit	> 5 g/kg
------	--------	----------

Skin corrosion/irritation Causes skin irritation.

Serious eye damage/eye irritation Causes serious eye irritation.

Respiratory or skin sensitization

Respiratory sensitization Not a respiratory sensitizer.

Skin sensitization May cause an allergic skin reaction.

Germ cell mutagenicity	No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.
Carcinogenicity	Not classifiable as to carcinogenicity to humans.
IARC Monographs. Overall Evaluation of Carcinogenicity	
d-limonene (CAS 5989-27-5)	3 Not classifiable as to carcinogenicity to humans.
OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)	
Not listed.	
US. National Toxicology Program (NTP) Report on Carcinogens	
Not listed.	
Reproductive toxicity	This product is not expected to cause reproductive or developmental effects.
Specific target organ toxicity - single exposure	Not classified.
Specific target organ toxicity - repeated exposure	Not classified.
Aspiration hazard	May be fatal if swallowed and enters airways.
Chronic effects	Prolonged inhalation may be harmful.

12. Ecological information

Ecotoxicity	Toxic to aquatic life with long lasting effects.
Persistence and degradability	No data is available on the degradability of any ingredients in the mixture.
Bioaccumulative potential	
Partition coefficient n-octanol / water (log Kow)	
d-limonene	4.57
Mobility in soil	No data available.
Other adverse effects	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal instructions	If discarded, this product is considered a RCRA ignitable waste, D001. Empty container can be recycled. Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Contents under pressure. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose in accordance with all applicable regulations.
Hazardous waste code	D001: Waste Flammable material with a flash point <140 F
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal.

14. Transport information

DOT

UN number	UN1950
UN proper shipping name	Aerosols, flammable, Limited Quantity
Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
Label(s)	2.1
Packing group	Not applicable.
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Special provisions	N82
Packaging exceptions	306
Packaging non bulk	304
Packaging bulk	None
Other information	
Passenger and cargo aircraft	Allowed with restrictions.
Cargo aircraft only	Allowed with restrictions.

IATA


UN number	UN1950
------------------	--------

UN proper shipping name Aerosols, flammable, Limited Quantity
Transport hazard class(es)
Class 2.1
Subsidiary risk -
Packing group Not applicable.
ERG Code 10L
Special precautions for user Read safety instructions, SDS and emergency procedures before handling.
Other information
Passenger and cargo aircraft Allowed with restrictions.
Cargo aircraft only Allowed with restrictions.

IMDG

UN number UN1950
UN proper shipping name AEROSOLS, Limited Quantity
Transport hazard class(es)
Class 2.1
Subsidiary risk -
Packing group Not applicable.
Environmental hazards
Marine pollutant Yes, but exempt from the regulations.
EmS F-D, S-U
Special precautions for user Read safety instructions, SDS and emergency procedures before handling.

DOT; IMDG



IATA



15. Regulatory information

US federal regulations This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not listed.

CERCLA Hazardous Substance List (40 CFR 302.4)

turpentine (CAS 9005-90-7)

CERCLA Hazardous Substances: Reportable quantity

turpentine (CAS 9005-90-7) 100 LBS

Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.

Food and Drug Administration (FDA) Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Classified hazard categories Flammable (gases, aerosols, liquids, or solids)
Gas under pressure
Skin corrosion or irritation
Serious eye damage or eye irritation
Respiratory or skin sensitization
Aspiration hazard

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical Yes

SARA 313 (TRI reporting)

Not regulated.

US state regulations

US. New Jersey Worker and Community Right-to-Know Act

carbon dioxide (CAS 124-38-9)

US. Massachusetts RTK - Substance List

carbon dioxide (CAS 124-38-9)

US. Pennsylvania Worker and Community Right-to-Know Law

carbon dioxide (CAS 124-38-9)
distillates (petroleum), hydrotreated light (CAS 64742-47-8)
turpentine (CAS 9005-90-7)

US. Rhode Island RTK

carbon dioxide (CAS 124-38-9)
distillates (petroleum), hydrotreated light (CAS 64742-47-8)

California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 2016 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins. For more information go to www.P65Warnings.ca.gov.

US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))

distillates (petroleum), hydrotreated light (CAS 64742-47-8)

Volatile organic compounds (VOC) regulations

EPA

VOC content (40 CFR 51.100(s)) 97.5 %

Consumer products (40 CFR 59, Subpt. C) Not regulated

State

Consumer products This product is regulated as a General Purpose Degreaser (aerosol). This product is compliant for use in all 50 states.

VOC content (CA) 9.8 %

VOC content (OTC) 9.8 %

International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	No
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	Yes
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	Yes
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
Taiwan	Taiwan Chemical Substance Inventory (TCSI)	Yes
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date	03-17-2020
Revision date	02-02-2021
Prepared by	Allison Yoon
Version #	02
Further information	CRC # 698A/1002746

Disclaimer The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC's knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries, Inc..

Revision information Product and Company Identification: Alternate Trade Names
Composition / Information on Ingredients: Component Summary
Physical & Chemical Properties: Multiple Properties
Disposal considerations: Disposal instructions
Disposal considerations: Hazardous waste code
GHS: Classification