



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2087W Radiant Dead FRNT Self Test Gfci 20A WH

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | 2087W |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Self-Test Gfci Receptacle Receptacle, 20 A, 125 V, 2 Poles, #14 to #10 Awg Compatible Wire Size, Control Circuit Actuator, Back and Side Wired Connection, 60 HZ, 1.73 In Width, 4.20 In Height, Thermoplastic Material, White, 0.025 Sec Trip Time, Impact Resistant, 0.2800 LB |
| Weight per unit | 0.2750 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|------------------|---------------------|
| actuator | Control Circuit |
| amperage rating | 20 |
| connection | Back and side wire |
| interrupt rating | 4 to 6 mA |
| Poles | 2 |
| trip range | 4 to 6 mA |
| Trip Type | .025 Second Nominal |
| Voltage Rating | 125 |

Dimensions and Weight

| | |
|--------|------|
| Length | 1.03 |
| Width | 1.73 |

Descriptions

| | |
|------------------------|---|
| Description | RADIANT DEAD FRNT SELF TEST GFCI 20A WH |
| extra long description | P&S 2087W RADIANT DEAD FRNT SELF TE |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Pass & Seymour |
| GTIN | 00785007035803 |
| UPC | 785007035803 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Residential Switches |
| Type | Specification Grade Dead-Front 20A Self-Test GFCI Receptacle |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.275 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|------------------------|
| environmental conditions | 95% Humidity, UL 94 V2 |
| Operating Temperature | -35°C to +66°C |
| standard | cULus, UL Listed, FSUL |