

# 2100 SERIES

SPECIFICATION GRADE  
1/2" CONDUIT MOUNTING  
DIE CAST ZINC  
PHOTOCONTROL



## APPLICATIONS

- Parking lot lighting
- Building perimeter lighting
- Outdoor signage

## FEATURES

**SENSOR:** Conformal coated cadmium sulphide photocell resists effects of moisture and airborne contaminants. Photocell responds to the light spectrum near to that of a human eye.

**OPERATION:** Delay of up to two minutes to prevent false switching due to light from passing vehicles, lightning, etc.

**STANDARDS:** Meets ANSI/UL773A.

**HOUSING:** Heavy Duty die cast zinc housing and base. Gasketed for maximum weather protection.

**ENERGY SAVINGS:** Works with screw base CFLs.

## SPECIFICATIONS

**ON/OFF:** Turn ON is 1 to 5fc, Turn OFF is 3 to 15fc, without the slide in position. ON/OFF adjustment is easily made by moving a slide cover. No tools required.

**TIME DELAY:** ON and OFF.

**CELL:** Cadmium sulphide, epoxy conformal coated 1" diameter.

**CONTACTS:** Remain closed between dusk and dawn. (The unit fails in the ON position).

**LEAD WIRES:** Three color coded, minimum 6" wire leads, #16AWG, rated for 105 °C.

**POWER CONSUMPTION:** Averages under 1 watt.


**TEMPERATURE RANGE:** -40 °F to +140 °F (-40 °C to +60 °C).

**FAIL MODE:** ON.

**WARRANTY:** 5 years.

CAT. NO.	UPC CODE	VOLTAGE (VAC) 50-60Hz	RATING		LED
			TUNGSTEN	BALLAST	
2101	60012	120	2000W	1800VA	600VA*
2104	60013	208-277	2000W	1800VA	600VA*
2107	60031	120/277	2000W	1800VA	600VA*
73866	62020	Mounting Bracket	-	-	-

\*LED rating for UL only.



# 2100 SERIES

SPECIFICATION GRADE  
1/2" CONDUIT MOUNTING  
DIE CAST ZINC  
PHOTOCONTROL



## APPLICATIONS

- Parking lot lighting
- Building perimeter lighting
- Outdoor signage

## FEATURES

**SENSOR:** Conformal coated cadmium sulphide photocell resists effects of moisture and airborne contaminants. Photocell responds to the light spectrum near to that of a human eye.

**OPERATION:** Delay of up to two minutes to prevent false switching due to light from passing vehicles, lightning, etc.

**STANDARDS:** Meets ANSI/UL773A.

**HOUSING:** Heavy Duty die cast zinc housing and base. Gasketed for maximum weather protection.

**ENERGY SAVINGS:** Works with screw base CFLs.

## SPECIFICATIONS

**ON/OFF:** Turn ON is 1 to 5fc, Turn OFF is 3 to 15fc, without the slide in position. ON/OFF adjustment is easily made by moving a slide cover. No tools required.

**TIME DELAY:** ON and OFF.

**CELL:** Cadmium sulphide, epoxy conformal coated 1" diameter.

**CONTACTS:** Remain closed between dusk and dawn. (The unit fails in the ON position).

**LEAD WIRES:** Three color coded, minimum 6" wire leads, #16AWG, rated for 105 °C.

**POWER CONSUMPTION:** Averages under 1 watt.

**TEMPERATURE RANGE:** -40 °F to +140 °F (-40 °C to +60 °C).

**FAIL MODE:** ON.

**WARRANTY:** 5 years.

CAT. NO.	UPC CODE	VOLTAGE (VAC) 50-60Hz	RATING		LED
			TUNGSTEN	BALLAST	
2101	60012	120	2000W	1800VA	600VA*
2104	60013	208-277	2000W	1800VA	600VA*
2107	60031	120/277	2000W	1800VA	600VA*
73866	62020	Mounting Bracket	-	-	-

\*LED rating for UL only.

