

ELLIOTT ELECTRIC SUPPLY We Deliver...Lower Cost, Quality Products, & Personal Service 1205 N Eliseo Felix Jr. Way Suite A101 85323-0000, AZ Avondale Phone: 623-259-1366 Fax: 623-259-1367



Weight Per each

31378 Aqua-Gel	li, 1-Quart Squeeze Bottle
Catalog Number	31378
Manufacturer	Ideal
Description	Lubricant, 1 QT Squeeze Bottle, Clear Blue, Mild Odor, Aqua-Gel I Lubricant, 0.98 Specific Gravity, +40 to +100 °F, 2.32 LB
Weight per unit	2.3 (lbs/each)
Product Category	Paint, Chemicals, Etc.
Dimensions and Weight Size	1
Descriptions Description	AQUA-GEL II, 1-QUART SQUEEZE BOTTLE
extra long description	IDEAL 31-378 Aqua-Gel Lubricant, Ide
Features Special Features	IDEAL Aqua-Gel II Non-toxic cable pulling lubricant in clear blue color is a polymer-based formula that offers maximum tension reduction in high-stress electrical and communications cable-pulling operations. Lubricant dries to a semi-fluid film that won't clog conduit, and cleans up easily with soap/water. It remains temperature stable over a wide temperature range from 28°F to 180°F (-2°C to 88°C). Lubricant is convenient to apply by hand, brush or pump. It is well suited with all cable types except compo Polymer-based formula provides maximum tension reduction in high-stress electrical and communication cable-pulling operations; Compatible with all cable types except composite
	rubber; Cleans up easily with soap and water; Clings to cable throughout long pulls; Remains stable over wide temperature range; Dries to a semi-fluid film that won't clog conduit; Easy to apply by hand, brush or pump; Environmentally safe - non-toxic, non-flammable and non-corrosive; For outdoor use only
Manufacturer Information	
Brand	Ideal
GTIN	00783250313785
UPC	783250313785
Taxonomies, Classifications, and Category Description	d Categories WIRE LUBE, MARKERS, & TIES
Туре	
Packaging	
Carton	1
Package	12
i dyndyy	

2.3167

1205 N Eliseo Felix Jr. Way Suite A101 85323-0000, AZ Avondale Phone: 623-259-1366 Fax: 623-259-1367

Uses, Certifications, and Standards	
standard	UL Listed