



Atlanta, Georgia

Phone 800-521-7326

Fax 770-745-1333

Lock Washer Zinc and Stainless



Peco Catalog#	Washer Size	A Inside Diameter		B Outside Diameter	(T+t)/2 Mean Section Thickness	W Section Width
		Min	Max	Max	Min	Min
		See Section Five of Our Catalog				
#4	0.1120	0.114	0.0120	0.209	0.025	0.040
#5	0.1250	0.133	0.1270	0.236	0.031	0.047
#6	0.1380	0.148	0.1410	0.250	0.031	0.047
#8	0.1640	0.174	0.1670	0.293	0.040	0.055
#10	0.1900	0.200	0.1930	0.334	0.047	0.062
#12	0.2160	0.227	0.2200	0.377	0.056	0.070
1/4	0.2500	0.260	0.2520	0.487	0.062	0.109
5/16	0.3120	0.322	0.3140	0.583	0.078	0.125
3/8	0.3750	0.385	0.3770	0.680	0.094	0.141
7/16	0.4380	0.450	0.4400	0.776	0.109	0.156
1/2	0.5000	0.512	0.5020	0.869	0.125	0.171
9/16	0.5620	0.574	0.5640	0.965	0.141	0.188
5/8	0.6250	0.641	0.6280	1.073	0.156	0.203
3/4	0.7500	0.766	0.7530	1.265	0.188	0.234
7/8	0.8750	0.894	0.8780	1.459	0.219	0.266
1	1.0000	1.024	1.0030	1.656	0.250	0.297
1-1/8	1.1250	1.153	1.1290	1.847	0.281	0.328
1-1/4	1.2500	1.280	1.2540	2.036	0.312	0.359
1-3/8	1.3750	1.408	1.3790	2.219	0.344	0.391
1-1/2	1.5000	1.534	1.5040	2.419	0.375	0.422
2	2.0000	2.039	2.0080	2.936	0.422	0.427

ASME B18.21.1-1994

	Regular	High-Alloy	18-8 Stainless	316 Stainless
Material	SAE 1055-1065 Carbon Steel	1/4"-1" 4037 Alloy Steel 1-1/8"-1-1/2" SAE 1055-1065 Carbon Steel	SAE 302 -305 Stainless	SAE 316 Stainless
Hardness	Rockwell C38 - 46	Rockwell C38 - 46	Rockwell C35 - 43	Rockwell C35 - 43

Peco Fasteners specification sheets are a reference guide to help in the selection of fasteners. Peco has made every effort to ensure the accuracy of the information. However, Peco Fasteners is not responsible for any errors that may be contained within these sheets. Peco Fasteners makes no claim of warranty in the accuracy of this information. Users of this information are solely responsible for protecting themselves against liability. It is solely the responsibility of the purchasers and users of these fasteners to consult with Engineers that are experts in an applicable field. Peco Fasteners is not responsible for any loss, claim, or damage due to these specification sheets.