



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2156 Rac 4" Emt Se Screw CPLG *Hubbell--Raco*

| | |
|------------------|--|
| Catalog Number | 2156 |
| Manufacturer | Hubbell--Raco |
| Description | RGD/Imc Set Screw Insulated Connectors Steel, 1 In. Trade Size |
| Weight per unit | 2.6 (lbs/each) |
| Product Category | Steel Set Screw Emt Couplings |

Features

| | |
|-------------------|-----------|
| Conduit Type | EMT |
| fitting type | Couplings |
| installation type | Screw |
| pallet quantity | 448 |
| Wall Thickness | 0.115 |

Material, Color, and Finish

| | |
|-------|--------|
| Color | Silver |
|-------|--------|

Dimensions and Weight

| | |
|--------|-------|
| Length | 4.724 |
|--------|-------|

Descriptions

| | |
|------------------------|--|
| Description | RAC 4" EMT SE SCREW CPLG |
| extra long description | RACO 2156 COUPLING RGD/EMT SET SCRE |
| Long Description | RGD/IMC Set Screw Insulated Connectors Steel, 1 In. Trade Size |
| Product Type | Commercial Fittings |
| Special Features | provides a concrete tight connection when taped;UL listed for use with Rigid/IMC conduit;zinc electro plated |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | RACO |
| GTIN | 00050169021569 |
| Manufacturers Part Number | 2156 |
| UPC | 050169021569 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------|
| Category Description | STEEL EMT FITTINGS |
| Type | Set screw coupling, EMT |

Trade Size

| | |
|------------|------|
| Trade Size | 4 in |
|------------|------|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight Per each | 2.578 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------------|------------------|
| Application | Electrical |
| standard | UL 514B |